




#### TECHNICAL CHARACTERISTICS

**MATERIAL**  
 INSULATOR: PA 66  
 FLAMABILITY RATING: UL94-V0  
 COLOR: GREEN  
 METAL HOUSING: BRASS (CuZn)  
 TERMINAL SCREW: STEEL ZINC PLATING "-" SLOT TYPE  
 WIRE GUARD: PbZ TIN PLATED

**ENVIRONMENTAL**  
 OPERATING TEMPERATURE: -40 UP TO 105°C  
 COMPLIANCE: LEAD FREE AND ROHS

|                       |             |        |
|-----------------------|-------------|--------|
| <b>ELECTRICAL</b>     | cULus       | VDE    |
| CURRENT RATING:       | 15A         | 17A    |
| WORKING VOLTAGE:      | 300VAC      | 300VAC |
| WITHSTANDING VOLTAGE: | 1.6KV       | 2.5KV  |
| CONTACT RESISTANCE:   | 20 mOhm MAX |        |

**STANDARD**  
 CERTIFIED E315414  
 CERTIFIED 40023402

**MECHANICAL**  
 SOLID WIRE: 24-12 AWG / 0.205-3.31 MM²  
 STRANDED WIRE: 24-12 AWG / 0.205-3.31 MM²  
 TORQUE: 3.5 Lb.In - 0.4 Nm

WIRE STRIPE LENGTH: 6-7 MM  
 SCREW: M3  
 PITCH: 5.08 MM

PACKAGING  
 BOX

| RoHS Compliant |           |                  |    |                                                                                                                       |                   |                                                                                                  | <div>SIZE</div> <div>A4</div> |
|----------------|-----------|------------------|----|-----------------------------------------------------------------------------------------------------------------------|-------------------|--------------------------------------------------------------------------------------------------|-------------------------------|
| G              | 12-JAN-15 | PROJECTION       | QP | <div>PROJECTION:</div> <div></div> | GENERAL TOLERANCE | <div></div> |                               |
| F              | 03-JAN-14 | UL & TEMP UPDATE | QL |                                                                                                                       | .X = $\pm$ 0.2    |                                                                                                  |                               |
| E              | 20-AUG-13 | DIM UPDATE       | QL |                                                                                                                       | .XX = $\pm$ 0.15  |                                                                                                  |                               |
| D              | 07-JUL-10 | NEW MEASURES     | GG |                                                                                                                       |                   |                                                                                                  |                               |
| C              | 29-MAR-10 | PLASTIC HOLDER   | JC | APPROVAL: FBr                                                                                                         | UNIT: MM          | DESCRIPTION: SERIE 352 - 5.08MM HORIZONTAL CABLE ENTRY PLUG WITH HOOK ON WIRE SIDE - WR-TBL      |                               |
| B              | 08-OCT-09 | NEW DRAW         | JP |                                                                                                                       | SCALE:            |                                                                                                  |                               |
| A              | 23-FEB-09 | PDF              | JP |                                                                                                                       | SHEET: 1/2        | WERI PART NO: 691 352 510 0xx                                                                    |                               |
| REV            | DATE      | FILE             | BY |                                                                                                                       | DRAW:             |                                                                                                  |                               |



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[691352510007](#)