



## Crystal Clock Oscillator Specification

*IQD Part No. + Packaging: LFSPX0056270Reel*

*Würth Part No. 831056270*



### Description

- Standard 2.5 x 2.0 oscillator in a ceramic package with a hermetically sealed metal lid.
- Model IQXO-794
- Model Issue number 1

### Frequency Parameters

- Frequency 26.0MHz
- Frequency Stability  $\pm 50.00\text{ppm}$
- Operating Temperature Range  $-40.00$  to  $85.00^\circ\text{C}$
- Ageing  $\pm 3\text{ppm}$  max per year

### Electrical Parameters

- Supply Voltage  $1.8\text{V} \pm 5\%$
- Current Draw  $10.000\text{mA}$

### Output Details

- Output Compatibility HCMOS
- Drive Capability  $15\text{pF}$
- Rise and Fall Time  $10.0\text{ns}$  max
- Duty Cycle  $40/60\%$
- Output Voltage High: 90% of VS min  
Output Voltage Low: 10% of VS max

### Output Control

- Standby Function (pin1):  
No Connection = Output Enabled  
>70% VS = Output Enabled  
<30% VS = Output Disabled  
(when disabled output goes to high impedance state)
- Start Up Time:  $10\text{ms}$  max

### Noise Parameters

- Jitter (Period pk-pk):  $\pm 80\text{ps}$  typ
- Jitter (Phase 12kHz to 20MHz):  $1\text{ps}$  max
- Jitter (Period One Sigma):  $\pm 10\text{ps}$  typ

### Environmental Parameters

- Shock: MIL-STD-202, Method 213. Or comparable.
- Vibration: MIL-STD-883, Method 2007. Or comparable.
- Storage Temperature Range:  $-55$  to  $125^\circ\text{C}$

### Compliance


- RoHS Status (2011/65/EU) Compliant
- REACH Status Compliant
- MSL Rating (JDEC-STD-033): Not Applicable

### Packaging Details

- Pack Style: Reel Tape & reel in accordance with EIA-481D  
Pack Size: 3,000



### Outline (mm)



### CONTACT INFORMATION:

Würth Elektronik eiSos GmbH & Co. KG  
Max-Eyth-Str. 1, 74638 Waldenburg, Germany  
Tel: +49(0) 7942 945-0

Email: [eiSos@we-online.de](mailto:eiSos@we-online.de)  
Web: [www.we-online.com](http://www.we-online.com)



## Crystal Clock Oscillator Specification

*IQD Part No. + Packaging: LFSPX0056270Reel*

*Würth Part No. 831056270*



- *Alternative packing option available*

### USEFUL LINKS

Toolbox:

[www.we-online.com/toolbox](http://www.we-online.com/toolbox)

Product Catalog:

[www.we-online.com/products](http://www.we-online.com/products)

### CONTACT INFORMATION:

Würth Elektronik eiSos GmbH & Co. KG  
Max-Eyth-Str. 1, 74638 Waldenburg, Germany  
Tel: +49(0) 7942 945-0

Email: [eiSos@we-online.de](mailto:eiSos@we-online.de)  
Web: [www.we-online.com](http://www.we-online.com)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Wurth Elektronik:](#)

[831056270](#)