


SHDSL LINE TRANSFORMERS



- Approved for use with Infineon's PEB22622, PEF22623 and PEF24622 SHDSL chipsets
- Excellent THD performance
- Designed to meet UL 1950 and EN 60950 requirements for supplementary insulation and 250 V working voltage

Electrical Specifications @ 25°C — Operating Temperature -40°C to +85°C

Part Number	Mounting	Turns Ratio (line - chip)	OCL Primary (mH $\pm 10\%$)	Leakage Inductance (μ H MAX)	DC Current Capability (mA)
B1063 ¹	SMT	3.2:1	3.0	25	60
B1093	THT				


Additional Specifications

Part Number	Turns Ratio (line - sense)	THD (Linearity)	DC Resistance		DCR Sense Winding (10-6)	Isolation Voltage (Vrms)
			Primary (1-5, 2-4 short)	Secondary (9-7)		
B1063 ¹	3.2:1	-75 dB MIN @ 3 KHz	4.0 Ω MAX	0.8 Ω MAX	5.0 Ω MAX	2000
B1093						


¹Transformers are shipped in tubes unless tape and reel is specified. Please add the suffix "T" (i.e. B1063T) for tape and reel orders.

Mechanicals

B1063




B1093



	B1063	B1093
Weight	6.2 grams	6.2 grams
Tape & Reel	150/reel	N/A
Tray/Tube	60/tray	60/tube
Dimensions: $\frac{\text{Inches}}{\text{mm}}$		
Unless otherwise specified, all tolerances are $\pm \frac{.010}{0.25}$		

Schematic



For More Information :

UNITED STATES (Worldwide)	UNITED KINGDOM (Northern Europe)	FRANCE (Southern Europe)	SINGAPORE (Southern Asia)	TAIWAN, R.O.C. (Northern Asia)	HONG KONG (China/Hong Kong)	DISTRIBUTOR
12220 World Trade Drive San Diego, CA 92128 U.S.A. http://www.pulseeng.com TEL: 858 674 8100 FAX: 858 674 8262	1 & 2 Huxley Road The Surrey Research Park Guildford, Surrey GU2 5RE United Kingdom TEL: 44 1483 401700 FAX: 44 1483 401701	Zone Industrielle F-39270 Orgelet France TEL: 33 3 84 35 04 04 FAX: 33 3 84 25 46 41	150 Kampong Ampat #07-01/02 KA Centre Singapore 368324 TEL: 65 6287 8998 FAX: 65 6280 0080	3F-4, No. 81, Sec. 1 HsinTai Wu Road Hsi-Chih, Taipei Hsien Taiwan, R.O.C. Tel: 886 2 2698 0228 FAX: 886 2 2698 0948	9/F, Phase 2, Tai Sang Shatin Warehouse Centre 6 Wong Chuk Yeung Street Fotan, Shatin, Hong Kong TEL: 852 2788 6588 FAX: 852 2776 1055	

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners.

Printed on recycled paper. ©2003, Pulse Engineering, Inc.

B993.A (12/03)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pulse:

[B1063T](#) [B1063](#)