



**Product:** [6139B8](#)

Surveillance CATV MATV, RG-11 #14 Sol BC, FFEP Core, Duofoil® + AL Braid, PVDF Jkt, CMP, CATVP

**Product Description**

Surveillance, CATV & MATV, RG-11, 14 AWG solid bare copper, foam FEP core, Duofoil® + 60% aluminum braid, PVDF jacket, CMP, CATVP

**Technical Specifications**

**Product Overview**

Suitable Applications:	CATV, MATV
------------------------	------------

**Construction Details**

RG Type:	11
----------	----

**Conductor**

Size	Stranding	Nom. Diameter	Material
14 AWG	Solid	0.064 in	BC - Bare Copper

**Insulation**

Material	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene (Foam)	0.274 in (6.96 mm)	White

**Outer Shield**

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
2	Braid	Aluminum		60%

**Outer Jacket**

Material	Nom. Diameter
PVDF - Polyvinylidene Fluoride	0.348 in (8.84 mm)

Overall Cable Diameter (Nominal):	0.348 in (8.84 mm)
-----------------------------------	--------------------

**Electrical Characteristics**

**Attenuation**

Frequency	Nom. Attenuation
1 MHz	0.17 dB/100ft
10 MHz	0.40 dB/100ft
50 MHz	1.00 dB/100ft
100 MHz	1.40 dB/100ft
200 MHz	2.30 dB/100ft
400 MHz	3.70 dB/100ft
700 MHz	5.30 dB/100ft
900 MHz	6.40 dB/100ft
1000 MHz	6.90 dB/100ft

**Electricals**

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
2.5 Ohm/1000ft	3.8 Ohm/1000ft (12 Ohm/km)	16.3 pF/ft (53.5 pF/m)	75 Ohm	83%

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating
150°C	-20°C to +150°C

Bend Radius

Installation Min.
3.5 in (89 mm)

Max. Pull Tension:	107 lbs (48.5 kg)
Bulk Cable Weight:	58 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor
Sustainability:	CA Prop 65, Product Lens™, Environmental Product Declaration (EPD) Available
Flammability / Reaction to Fire:	NFPA 262
NEC / UL Compliance:	CATVP, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.479 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
6139B8 0091000	White	Reel	1,000 ft	612825173816	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[6139B8 0091000](#)