



Product: [8020](#)

Bus Bar Wire, #20 Sol TC

Request Sample

Product Description

Bus Bar Wire, 20AWG (Solid) Tinned Copper, QQ-W-343G

Technical Specifications

Product Overview

Suitable Applications:	bus bar
------------------------	---------

Construction Details

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	1	20	Solid	TC - Tinned Copper

Overall Cable Diameter (Nominal):	0.032 in (0.81 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals
Nom. Conductor DCR
10.2 Ohm/1000ft

Mechanical Characteristics

Bend Radius	
Stationary Min.	Installation Min.
0.13 in (3.3 mm)	0.13 in (3.3 mm)

Max. Pull Tension:	12.4 lbs (5.62 kg)
Bulk Cable Weight:	3 lbs/1000ft

Standards and Compliance

Sustainability:	CA Prop 65
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

History

Update and Revision:	Revision Number: 0.441 Revision Date: 07-03-2024
----------------------	--------------------------------------------------

Part Numbers

Item #	Color	Putup Type	Length	UPC
8020 000100	None	Reel	100 ft	612825194323
8020 0001000	None	Reel	1,000 ft	612825194330

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[8020 000100](#) [8020 0001000](#)