


PICMG Backplanes

PICMG® 1.3 Backplanes




EBP-5E1

PCI-E® x16	1	PICMG®	1
PCI-E® x4		AT	
PCI-X™	1	ATX	Yes
PCI™	2	Segments	1
Dimensions	153 mm x 330 mm		




EBP-7E2

PCI-E® x16	1	PICMG®	1
PCI-E® x4	1	AT	
PCI-X™		ATX	Yes
PCI™	4	Segments	1
Dimensions	328 mm x 206 mm		




EBP-9E2

PCI-E® x16	1	PICMG®	1
PCI-E® x4	1	AT	
PCI-X™		ATX	Yes
PCI™	6	Segments	1
Dimensions	328 mm x 206 mm		



EBP-D3E1


PCI-E® x16		PICMG®	1
PCI-E® x4	1	AT	
PCI-X™		ATX	Yes
PCI™		Segments	1
Dimensions	331 mm x 39 mm		



EBP-D3S1


PCI-E® x16		PICMG®	1
PCI-E® x4		AT	
PCI-X™		ATX	Yes
PCI™	1	Segments	1
Dimensions	331 mm x 39 mm		

PICMG Backplanes




EBP-1UX4

PCI-E® x16		PICMG®	1
PCI-E® x4	2	AT	
PCI-X™		ATX	Yes
PCI™	4	Segments	1
Dimensions	414 mm x 39 mm		




EBP-D5E2

PCI-E® x16	1	PICMG®	1
PCI-E® x4	1	AT	
PCI-X™		ATX	Yes
PCI™	2	Segments	1
Dimensions	331 mm x 84 mm		




EBP-10E5

PCI-E® x16	1	PICMG®	1
PCI-E® x4		AT	
PCI-E® x1	4	ATX	Yes
PCI™	4	Segments	1
Dimensions	330 mm x 318 mm		




EBP-13E2

PCI-E® x16	1	PICMG®	1
PCI-E® x4	1	AT	
PCI-X™		ATX	Yes
PCI™	10	Segments	1
Dimensions	330mm x 318mm		



EBP-13E4


PCI-E® x16	1	PICMG®	1
PCI-E® x4	3	AT	
PCI-X™		ATX	Yes
PCI™	7	Segments	1
Dimensions	330 mm x 318 mm		



EBP-16Q8


PCI-E® x16	4	PICMG®	4
PCI-E® x4	4	AT	
PCI-X™		ATX	Yes
PCI™	4	Segments	4
Dimensions	328 mm x 416 mm		

PICMG Backplanes



HPCI-D3S2

PICMG®	1	AT	
PCI™	2	ATX	Yes
ISA		Segments	1
Dimensions	261 mm x 39 mm		



HPCI-D6S4

PICMG®	1	AT	Yes
PCI™	4	ATX	Yes
ISA	1	Segments	1
Dimensions	261 mm x 79.6 mm		




HPCI-6S4

PICMG®	1	AT	Yes
PCI™	4	ATX	Yes
ISA	1	Segments	1
Dimensions	264.2 mm x 132.7 mm		




HPCI-8S4

PICMG®	2	AT	Yes
PCI™	4	ATX	Yes
ISA	4	Segments	1
Dimensions	264.2 mm x 218 mm		




HPCI-9S7U

PICMG®	2	AT	Yes
PCI™	7	ATX	Yes
ISA	2	Segments	1
Dimensions	213.4 mm x 259.1 mm		




HPCI-13S4LU

PICMG®	3	AT	Yes
PCI™	4	ATX	Yes
ISA	9	Segments	1
Dimensions	314.7 mm x 259 mm		




HPCI-14S7U

PICMG®	3	AT	Yes
PCI™	7	ATX	Yes
ISA	7	Segments	1
Dimensions	314.7 mm x 259.1 mm		




HPCI-14S12U

PICMG®	2	AT	Yes
PCI™	12	ATX	Yes
ISA	2	Segments	1
Dimensions	314.7 mm x 259 mm		




HPCI-14S/ATX

PICMG®	2	AT	Yes
PCI™	4	ATX	Yes
ISA	9	Segments	1
Dimensions	312 mm x 265 mm		




HPCI-15S

PICMG®	2	AT	Yes
PCI™	4	ATX	Yes
ISA	10	Segments	1
Dimensions	317 mm x 264.2 mm		



HPCI-15S10

PICMG®	2	AT	Yes
PCI™	10	ATX	Yes
ISA	4	Segments	1
Dimensions	317 mm x 264.2 mm		



HPCI-19S18A

PICMG®	2	AT	Yes
PCI™	18	ATX	Yes
ISA	1	Segments	1
Dimensions	415.3 mm x 264.2 mm		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ADLINK Technology:

[HPCI-15S](#) [HPCI-D3S2](#) [HPCI-14S/ATX](#) [HPCI-6S4](#) [HPCI-13S4LU](#) [HPCI-9S7U](#) [HPCI-6S](#) [HPCI-14S7U](#) [HPCI-D6S4](#)
[HPCI-19S18A](#) [HPCI-8S4](#) [HPCI-15S10](#) [HPCI-14S12U](#)