


Lennox/Allied Air

HSI & Spark Single Stage Furnace Control Kits

D
OEM Direct

50M56U-801

Integrated Furnace Control



- 120V HSI Ignition
- PSC Blower Motor

Replaces 81W03, 56W19, 94W83 and 74W03 Lennox Family Control Platforms

50D50-801

Non-Integrated Ignition Module



- Intermittent/Proven Pilot Spark Ignition
- Direct and Indirect Flame Sense

Replaces 30W33 Kit on G20/G20R/G23/G26 Furnaces

Direct Replacement is Fast and Easy.

Kits ensure continued peak system performance.

White-Rodgers™

EMERSON™

HSI & Spark Single Stage Furnace Control Kits

50M56U-801

Integrated Control

Features

- 120V Ignitor Output
- Heat, Cool, Fan Only PSC Blower Speeds
- Diagnostic LED with Fault Recall
- Mounts Using OEM Standoff Locations
- Agency Approved
- Adapter Harness for Application Flexibility

Dip Switch Adjustable Timings (seconds)

Heat Delay-To-Fan-On	Heat Delay-To-Fan-Off	Cool Delay-To-Fan-On	Cool Delay-To-Fan-Off
30*/45	60/90/120*/180	2	2/60*

*Default setting

Cross Reference

Lennox, Armstrong, AirEase, Concord, Ducane, Aire-Flo	
100973-01*	12L4201
100973-02*	17W70*
1012-83-9673A	50A55-120
1012-967	56L8501
1012-968	56W19
1012-969*	74W03
1012-969A*	75M1701*
1012-977A	78M1701*
103085-01	78M4701*
103085-02	80M2701
103085-03	81W03*
103098-01	81W11
1195-83-100A	94W83
1195-100	R47582-001

*Requires 120V Ignitor (21D64-2)

50D50-801

Non-Integrated Module

Features

- Intermittent/Proven Pilot Spark Ignition
- Direct and Indirect Flame Sense
- Diagnostic LED
- Mounts Using Supplied Bracket in OEM Location
- Agency Approved
- All Required Conversion Accessories Included

Cross Reference

Lennox, Armstrong, Ducane	
18G91	65K9301
18G9101	69J36
28L49	69J3601
28L4901	74H26
30W33	74H2601
30W3301	80N92
34G66	80N9201
34G6601	93K21
38707B001	93K2101
41K87	97H04
41K8701	97H0401
48K99	LB-90087A
48K9901	LB-90701A
53L90	LB-90701B
53L9001	LB-90701C
63K24	LB-9071B
63K2401	LB-92869A
65K93	
Johnson Controls	
G776RDG-1	G776RDG-11
G776RDG-2	G776RDG-14
G776RDG-10	
Robertshaw	
SP735L	SP745
Honeywell	
S8660K1006	
ICM	
ICM2902	ICM293

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[White-Rodgers:](#)

[50D50-801](#) [50M56U-801](#)