



Product: [1506ABHD1](#)

6 GHz RG59 BNC Connector

Product Description

RG-59, 6 GHz, HD, BNC, Plenum, 1 piece connector

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Suitable Applications: | HD-SDI, Video, Digital Video, SMPTE 2081-1 6 Gb/s UHDTV, SMPTE 424M 3 Gb/s HD-SDI 1080P |
|------------------------|---|

Physical Characteristics (Overall)

| | |
|------------|----------------|
| Packaging: | 50 per package |
|------------|----------------|

Connectors

Materials

| Description | Material |
|-------------|----------------------|
| Nut | Brass, Nickel Plated |
| Body | Brass, Nickel Plated |
| Contact | Brass, Gold Plated |
| Insulator | PTFE |

Electrical Characteristics

Impedance

| Nominal Characteristic Impedance |
|----------------------------------|
| 75 Ohm |

Return Loss (RL)

| Frequency [MHz] | Minimum Return (RL) |
|-----------------|---------------------|
| 5-1485 | 15 dB |
| 1485-3000 | 10 dB |
| 3000-4500 | 7 dB |

| | |
|-----------------------------------|---|
| Electrical Characteristics Notes: | SMPTE 2081-1 Return Loss or better to 4.5 GHz |
|-----------------------------------|---|

Mechanical Characteristics

| | |
|---------------------------|---|
| Footprint/Type: | Coax |
| Connector Interface Type: | BNC |
| Connector Series Name: | HD |
| Locking: | No |
| Tool Compatibility: | CPLCRBC-BR (compression), PSA59/6 (strip) |
| Termination Type: | Compression |

Standards

| | |
|----------|----|
| RG Type: | 59 |
|----------|----|

Applicable Environmental and Other Programs

| | |
|--|-------------------------------|
| Environmental Space: | Indoor |
| EU Directive 2000/53/EC (ELV): | Yes |
| EU Directive 2011/65/EU (RoHS 2): | Yes |
| EU Directive 2012/19/EU (WEEE): | Yes |
| EU Directive 2015/863/EU (RoHS 2 amendment): | Yes |
| EU Directive Compliance: | EU Directive 2003/11/EC (BFR) |

Suitability

| | |
|------------------------|-----|
| Suitability - Indoor: | Yes |
| Suitability - Outdoor: | No |

Related Part Numbers

Variants

| Item # | Color | UPC |
|-----------|-------|--------------|
| 1506ABHD1 | Red | 845671002393 |

| | |
|-----------|---|
| Footnote: | Q - STANDARD PACKAGES CANNOT BE BROKEN. |
|-----------|---|

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.119 Revision Date: 03-04-2023 |
|----------------------|--|

© 2024 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[1506ABHD1](#)