

AX101472 Faceplates and Panels - 12-CONNECTOR GIGABIX MOUNT



For more Information
please call

1-800-Belden1

**General Description:**

12-CONNECTOR GIGABIX MOUNT (EMPTY), BLACK

Usage (Overall)

Suitable Applications:	IBDN System 4800, 3600, 2400, TIA Category 6, ISO Class E, 1000BASE-T
Related Parts:	GigaBIX Connectors, Management Ring, Management Module, Patchcord Organizer, Horizontal channel plate, GigaBIX Patchcord, GigaBIX/MediaFlex Adapter

Physical Characteristics (Connectivity)**Capacity**

Max. Capacity:	12 GigaBIX Connectors to be ordered separately
----------------	--

Access

Front Connection:	Flush
Termination Area:	Front and Rear

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
15.281	7.639	4.527

Materials

Materials:

Description	Material
Panel	Steel

Color

Color:	Black
--------	-------

Weight

Weight:	10.900 lbs.
---------	-------------

Included Parts

Included Parts:	2 Wood Screws
-----------------	---------------

Packaging

Packaging:	Individually packaged in a cardboard box.
------------	---

Mechanical Characteristics (Connectivity)

Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/30/2008
Safety Listing:	ACA, Bi-national Standard Listed

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Transmission Characteristics (Connectivity)**Notes (Overall)**

Notes: Refer to Installation Guide PX101814 (English) and PX101813 (French) or visit our web site at <http://www.belden.com>

Product Family

Part Numbers:

AX101472 Faceplates and Panels - 12-CONNECTOR GIGABIX MOUNT

Description	Item Number
GigaBIX Termination Kit - 72 ports	AX101470
GigaBIX Termination Kit - 300 pairs	AX101471
GigaBIX Rack Mount Termination Kit - 48 ports	AX101985

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX101472	1 EA	10.910 LB			GIGABIX MOUNT,12-CONN,(EMPTY)

Revision Number: 0 Revision Date: 10-14-2016

© 2018 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumberg Automation:](#)

[AX101472](#)