



**Product:** [9976](#)

Lead Wire, #26 Sol TC, PVC Ins, AWM 1061

[Request Sample](#)

**Product Description**

Low Temp Plastic Lead Wire, 26AWG (Solid) Tinned Copper, PVC Insulation, AWM 1061 CSA AWM 300V 80C

**Technical Specifications**

**Product Overview**

Suitable Applications:	inter-connection circuits, internal wiring of computer and electronic equipments, wire wrap applications
------------------------	----------------------------------------------------------------------------------------------------------

**Physical Characteristics (Overall)**

Conductor			
AWG	Stranding	Material	No. of Conductors
26	Solid	TC - Tinned Copper	1
Conductor Count:			1

<b>Insulation</b>		
Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.036 in	0.01 in

**Electrical Characteristics**

<b>Voltage</b>	
UL Voltage Rating	
300 V RMS	

**Temperature Range**

Non-UL Temp Rating:	80°C
UL Temp Rating:	80°C

**Mechanical Characteristics**

Bulk Cable Weight:	1.25 lbs/1000ft
Min. Bend Radius/Minor Axis:	0.15 in

**Standards**

UL Rating:	300V RMS, 80°C
UL AWM Style Compliance:	AWM 1061
CSA Rating:	300V RMS, 80°C
CSA AWM Compliance:	CSA AWM I A/B
CSA Type:	AWM I, A/B

**Applicable Environmental and Other Programs**

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes

EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
CA Prop 65:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
CSA Flammability:	FT1
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length	UPC
9976 010100	Black	Reel	100 ft	612825265672
9976 0101000	Black	Reel	1,000 ft	612825265689
9976 0131000	Blue, Dark	Reel	1,000 ft	612825265696
9976 0011000	Brown	Reel	1,000 ft	612825265566
9976 0081000	Gray	Reel	1,000 ft	612825265634
9976 0051000	Green, Dark	Reel	1,000 ft	612825265627
9976 0031000	Orange	Reel	1,000 ft	612825265597
9976 002100	Red	Reel	100 ft	612825265573
9976 0021000	Red	Reel	1,000 ft	612825265580
9976 009100	White	Reel	100 ft	612825265658
9976 0091000	White	Reel	1,000 ft	612825265665
9976 0041000	Yellow	Reel	1,000 ft	612825265603

Footnote:	P - STRIPE COLORS ON STOCK SOLID COLORS. STRIPING ADDER OF \$8.00/M= FOR 1 OR 2 STRIPES. 10,000' MINIMUM ORDER FOR COLOR COMBINATION. PUT-UP WILL BE SUBJECT TO TWO PIECES (+ OR -) 10% PER SPOOL, WITH A MINIMUM LENGTH OF 100'.
-----------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

History

Update and Revision:	Revision Number: 0.368 Revision Date: 05-05-2023
----------------------	--------------------------------------------------

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[9976 0131000](#) [9976 0081000](#) [9976 002100](#) [9976 0091000](#) [9976 009100](#) [9976 0101000](#) [9976 010100](#) [9976](#)  
[0011000](#) [9976 0021000](#) [9976 0051000](#)