

Product: M-SFP-10-LR/LC EEC



SFP Fiberoptic 10 Gigabit Ethernet Transceiver SM, extended temperature range

Product Description

SFP Fiberoptic 10 Gigabit Ethernet Transceiver SM with LC connector, extended temperature range

Technical Specifications

Product description

Туре:	M-SFP-10-LR/LC EEC	
Description:	SFP Fiberoptic 10 Gigabit Ethernet Transceiver SM, extended temperature range	
Part Number:	942211001	
Port type and quantity:	1 x 10000 Mbit/s with LC connector	
Network size - length of cable		
Single mode fiber (SM) 9/125 µm:	typ. 10 km (Link budget at 1310 nm = 0-7.4 dB; 0.4 db/km, 3.5 ps/ (nm*km)	
Power requirements		
Operating Voltage:	power supply via the switch	

Power consumption:

Software

- Diagnostics:
- Optical input and output power, transceiver temperature

1 W

Ambient conditions

MTBF:	2466 years (Telcordia SR-332, Issue 2, 40°C)
MTBF (Telecordia SR-332 Issue 3) @ 25°C:	2466 Years
Operating temperature:	-40-+85 °C
Storage/transport temperature:	-40-+85 °C
Relative humidity (non-condensing):	5-95 %

Mechanical construction

Dimensions (WxHxD):	20 mm x 18 mm x 50 mm
Weight:	74 g
Mounting:	SFP+ slot
Protection class:	IP20

Mechanical stability

IEC 60068-2-6 vibration:	1 mm, 2 Hz-13.2 Hz, 90 min.; 0.7 g, 13.2 Hz-100 Hz, 90 min.; 3.5 mm, 3 Hz-9 Hz, 10 cycles, 1 octave/min.; 1 g, 9 Hz-150 Hz, 10 cycles, 1 octave/min
IEC 60068-2-27 shock:	15 g, 11 ms duration, 18 shocks

EMC interference immunity

EN 61000-4-2 electrostatic discharge (ESD):	6 kV contact discharge, 8 kV air discharge
EN 61000-4-3 electromagnetic field:	10 V/m (80-1000 MHz)
EN 61000-4-4 fast transients (burst):	2 kV power line, 1 kV data line
EN 61000-4-5 surge voltage:	power line: 2 kV (line/earth), 1 kV (line/line), 1 kV data line

EN 61000-4-6 Conducted Immunity:	3 V (10 kHz-150 kHz), 10 V (150 kHz-80 MHz)	
EMC emitted immunity		
EN 55022:	EN 55022 Class A	
FCC CFR47 Part 15:	FCC 47CFR Part 15, Class A	
Approvals		
Safety of information technology equipment:	EN60950	
Hazardous locations:	depending on deployed switch	
Shipbuilding:	depending on deployed switch	
Scope of delivery and accessories		
Scope of delivery:	SFP module	
Further Instructions		
Product Documentation:	https://www.doc.hirschmann.com	
Certificates:	https://www.doc.hirschmann.com/certificates.html	
Variants		
Item # Type 942211001 M-SFP-10-LR/LC EEC		
Update and Revision:	Revision Number: 0.75 Revision Date: 11-09-2022	

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Hirschmann: M-SFP-10-LR/LC EEC