

**E502001 Cord Sets - DataTuff® Cat 5e IP67 RJ45 Cord Set**

For more Information  
please call

1-800-Belden1

**General Description:**

1 meter (3.3 ft.), Unshielded with stranded conductors (ref: Belden Bonded-Pair Cable 7924A). Cable Rating NEC: CMR, CMX-Outdoor. CEC: CMR FT4. MSHA.

**Applicable Specifications and Agency Compliance (Overall)****Applicable Standards & Environmental Programs**

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2006
MII Order #39 (China RoHS):	EUP 50

**Notes (Overall)**

**Notes:** For additional information about this product, visit our web site at <http://www.belden.com>

**Cable**

<b>Description:</b>	4 pair, 24 AWG Stranded (7x32) Tinned Copper, Polyolefin Insulation, Bonded
<b>Part Number:</b>	7924A
<b>Shielding:</b>	Unshielded
<b>Electrical Performance:</b>	Category 5ePatch
<b>Maximum Operating Voltage:</b>	300 V RMS
<b>Applicable Standards:</b>	ANSI/TIA/EIA-568-C.2, ISO/IEC 11801, UL 1666 Riser

**Connectors**

<b>Description:</b>	Encapsulated RJ45 plugs. Suitable for use in IP67 sealed applications
<b>Connector Type:</b>	Cat 5e
<b>Connector Materials:</b>	UL94V-0 flame retardent
<b>Sealing:</b>	Suitable for IP67
<b>Connector Interface:</b>	IEC 60603-7
<b>Encapsulation Interface:</b>	IEC 61076-3-106
<b>Tethered Cap:</b>	Yes
<b>Shielding:</b>	Unshielded
<b>Electrical Performance:</b>	Cat 5e
<b>Maximum Operating Voltage:</b>	300 V RMS
<b>Applicable Standards:</b>	ANSI/TIA/EIA-568-C.2, ISO/IEC 11801, EtherNet/IP Specification

**Assembly**

<b>Part Number:</b>	E502001
<b>Electrical Performance:</b>	Cat 5e Patch
<b>Maximum Operating Voltage:</b>	300 V RMS
<b>Storage Temperature Range:</b>	-40°C To +70°C

**E502001 Cord Sets - DataTuff® Cat 5e IP67 RJ45 Cord Set**

<b>Installation Temperature Range:</b>	-10°C To +60°C
<b>Operating Temperature Range:</b>	-10°C To +60°C
<b>Temperature Rating:</b>	70°C
<b>Applicable Standards:</b>	ANSI/TIA/EIA-568-C.2, ISO/IEC 11801, UL 1863 and CSA-22.2 No. 233
<b>Shielding:</b>	Unshielded
<b>Length:</b>	1 meter (3.3 ft.)
<b>Notes:</b> US Patent #'s 5, 606, 151; 5, 734, 126. EtherNet/IP is a trademark of ControlNet	

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
E502001 010S1	1 EA	0.251 LB	BLACK		CORSET IP67 C5E UTP STR 1M BK

Revision Number: 1    Revision Date: 12-13-2013

© 2019 Belden, Inc  
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Belden Wire & Cable:](#)

[E502001 010B50](#) [E502001 010S1](#)