

MODEL TL-5955



International size reference: 2/3AA, ER14335

TECHNICAL DATA

(Typical values @+ 25°C for batteries stored for one year or less)



■ Nominal capacity @ 1.3 mA, to 2 V	1.5 Ah
■ Rated voltage	3.6 V
■ Maximum recommended continuous current	75 mA
■ Maximum pulse current capability	150 mA
■ Weight	12.5 g (0.441 oz)
■ Volume	5.2 cc
■ Operating temperature range	-55 °C to +85 °C
■ Li metal content	approx. 0.5 g
■ U.L. Component Recognition, MH 12193	

TADIRAN
LITHIUM
BATTERIES



TERMINATIONS & ORDERING NO.

SUFFIX- /S STANDARD	15-5955-21500
SUFFIX- /T SOLDER TABS	15-5955-31500
SUFFIX- /P AXIAL PINS	15-5955-41500
SUFFIX- /PT2 RADIAL PINS	15-5955-36500
SUFFIX- /TP POLARIZED TABS	15-5955-52500
SUFFIX- /PT POLARIZED TABS	15-5955-53500




iXtra - Long Term High Performance

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance. ECN 1501879 Rev. D 11/08

TL-5955

CELL FEATURES

- 3.6 V Primary lithium-thionyl chloride (Li-SOCl₂)
- Fast voltage recovery after long term storage and/or usage
- High energy density
- High and stable operating voltage
- Low self discharge rate
- Bobbin construction
- Hermetic glass-to-metal-sealing
- Non-flammable electrolyte



TADIRAN LITHIUM BATTERIES



MAIN APPLICATIONS

- Utility meters (elect., water & gas)
- Automatic meter reading
- RF systems
- Sensors & monitoring systems
- Tracking systems
- Wireless security systems
- Automotive electronics
- Industrial electronics
- Ultra Low Power (ULP)

STORAGE CONDITIONS

- Cells should be stored in a clean & dry (less than 30 % RH) area

For updated information please visit our website www.tadiranbat.com



iXtra - Long Term High Performance

Note: Any presentations in this data sheet concerning performance are for information purpose only and are not construed as warranties either expressed or implied, of future performance.

ECN 1501879 Rev. D 11/08

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Tadiran Batteries:

[TL5955/T](#) [TL5955/S](#) [TL5955/P](#) [TL5955/TP](#) [TL5955/PT](#) [TL-5955/PBP](#) [TL-5955/TBP](#)