

Full or partial part number

Home / LED Indication / Flexible Light Pipes / FLP System



Flexible Light Pipes, LED Indication

FLP System

Available Options:

Adapter LED

Color/Wavelength

Red 625nm / Green 568nm

▼

Adapter Optical Fiber

Diameter

2mm

▼

Lens Size

5.1mm

▼

Lens Profile

Low Profile

▼

Panel Cutout

Round

▼

Luminous Intensity

8mcd/8mcd

▼

Optical Fiber Length

2.0 in.

▼

Optical Fiber Color

Blue

▼



Part Number:

FV4-2.0-BC-F5P-6

Categories: FLEXIBLE LIGHT PIPES ,

LED INDICATION

Request Sample

Check Stock

Download Data Sheet

Download 3D Drawing

Download RoHS Docs

View List →

Additional information

Adapter LED Color/Wavelength	Amber/605nm, Amber/620nm, Blue/466nm, Blue/470nm, Green/563nm, Green/568nm, Green/570nm, Green568nm, N/A, Orange/620nm, Red 625nm / Green 568nm, Red 625nm/Green 568nm, Red 645nm / Green 568nm, Red/625nm, Red/640nm, Red/640nmnm, Red/645nm, Red/660nm, Turquoise/500nm, White/6000K, White/6500K, Yellow 585nm / Green 565nm, Yellow 585nm/Green 565nm, Yellow 590nm / Green 568nm, Yellow 590nm/Green 515nm, Yellow 590nm/Green 568nm, Yellow 590nm/Green568nm, Yellow/585nm, Yellow/588nm, Yellow/590nm
Adapter Optical Fiber Diameter	1mm, 2mm
Lens Size	3.2 x 6.4 mm, 3.2mm x 6.4mm, 4.0mm, 4.2mm, 5.1mm, 6.0mm IP67, 6.7mm x 4.2mm, 7.0mm, 9.0mm IP67, N/A
Lens Profile	Dome, Flat, Low Profile, Low Profile Diffused, Low Profile Fresnel, N/A
Panel Cutout	N/A, Oval, Rectangular, Round
Luminous Intensity	100mcd/60mcd, 120mcd, 15/5 mcd, 1500mcd, 15mcd/5mcd, 200mcd, 2200mcd, 250mcd, 300mcd, 350mcd, 400/80 mcd, 400mcd, 50mcd, 50mcd/50mcd, 6000mcd, 600mcd, 60mcd, 65mcd, 6mcd/8mcd, 70mcd, 800mcd, 8mcd/8mcd, 900mcd, N/A
Optical Fiber Length	1.0 in., 1.5 in., 10.0 in., 100.0 in., 118.0 in., 12.0 in., 12.3 in., 13.0 in., 14.0 in., 15.0 in., 18.0 in., 2.0 in., 2.1 in., 2.3 in., 2.5 iin., 2.5 in., 2.9 in., 24.0 in., 3.0 in., 3.25 in., 3.28 in., 3.5 in., 3.9 in., 36.0 in., 4.0 in., 4.1 in., 4.5 in., 5.0 in., 6.0 in., 6.5 in., 6.7 in., 8.0 in., 9.0 in., 9.5 in., N/A
Optical Fiber Color	Black, Blue, Green, N/A, Red, White, Yellow



Keep up with Bivar

Email*

Subscribe

BIVAR CORPORATE OFFICE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[BIVAR:](#)

[FV4-2.0-BC-F5P-6](#)