


NOTES:

1. BEZEL MATERIAL IS NYLON 6/6, UL94 V-0
2. DOUBLE-SIDED ADHESIVE TAPE MATERIAL IS KRAFT PAPER WITH 3M 9482.
3. LIGHT PIPE IS CLEAR POLYCARBONATE, UL94 V-0.
4. PLP2-XXXX LIGHT PIPES ARE PACKAGED AND SHIPPED UNASSEMBLED.




REVISIONS			
REV.	DESCRIPTION	DATE	APPROVED
A	ENGINEERING RELEASE	07/19/23	A.V.

PITCH (ROW-COLUMN)
 NO OF COLUMNS
 NO. OF ROWS
 BEZEL MOUNT
 LIGHT PIPE LENGTH

P/N: MLPS - B - 3 - HHJJ - KK - T - PLP2-XXXX

ARRAY CONFIGURATION		PITCH (ROW - COLUMN) "KK"			BEZEL MOUNT "T"	LIGHT PIPE LENGTH	
ROWS "HH"	COLUMNS "JJ"	PITCH	ROW "K_"	COLUMN "_K"		LENGTH	CODE "XXXX"
01	01	0.000 IN 0.200 IN	0 C	0 C	2		
02	02				4	.188 IN	188
03	03				6	.215 IN	215
04	04				8	.250 IN	250
05	05	0.200 IN	C	C	10	.313 IN	313
06	06				12	.350 IN	350
07	07				14	.375 IN	375
08	08					.500 IN	500
09	09					.625 IN	625
10	10					.750 IN	750
11	11					1.000 IN	1000
12	12					1.200 IN	1200
	13					5.0 mm	5MM
	14					6.0 mm	6MM
						7.0 mm	7MM
						8.0 mm	8MM
						9.0 mm	9MM
						10.0 mm	10MM



PART NO. EXAMPLE:

MLPS-B-3-0205-CC-2-PLP2-375

2 ROWS, 5 COLUMNS
 .200 X .200 PITCH (ROW-COLUMN)
 2 BEZEL MOUNTS
 PLP2-375 LIGHT PIPE

CUSTOMER USE DRAWING

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
DECIMALS	ANGULAR		
.X ± .1	X° ± 1°	TITLE: MODULAR LIGHT PIPE SYSTEM, BEZEL, PLP2-XXXX	
.XX ± .01		DESIGNED: A.VALDEZ	DATE: 07/19/2023
.XXX ± .005		REVISION: A	REVISION: A
		CAGE CODE: 32559	
		SHEET SIZE A	
CHECKED: MICHAEL P.	DATE: 07/19/2023	SCALE: N/A	SHEET # 1 OF 1

CAD GENERATED DOCUMENT, DO NOT MEASURE DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[MLPS-B-3-0106-C0-2-PLP2-215](#) [MLPS-B-3-0201-CC-2-PLP2-215](#) [MLPS-B-3-0206-CC-2-PLP2-215](#) [MLPS-B-3-0304-CC-2-PLP2-215](#) [MLPS-B-3-1206-CC-10-PLP2-215](#) [MLPS-B-3-0202-CC-2-PLP2-215](#) [MLPS-B-3-0104-C0-2-PLP2-215](#) [MLPS-B-3-1206-CC-12-PLP2-215](#) [MLPS-B-3-0106-C0-2-PLP2-250](#) [MLPS-B-3-0304-CC-2-PLP2-250](#) [MLPS-B-3-0206-CC-2-PLP2-250](#) [MLPS-B-3-1206-CC-12-PLP2-313](#) [MLPS-B-3-0202-CC-2-PLP2-250](#) [MLPS-B-3-0201-CC-2-PLP2-313](#) [MLPS-B-3-0101-C0-2-PLP1-7MM](#) [MLPS-B-3-0101-C0-2-PLPC3-188](#) [MLPS-B-3-0101-C0-2-PLPC3-5MM](#) [MLPS-B-3-0101-C0-2-PLPC3-7MM](#) [MLPS-B-3-0102-C0-2-PLP1-9MM](#) [MLPS-B-3-0103-C0-2-PLP2-1000](#) [MLPS-B-3-0103-C0-2-PLP2-500](#) [MLPS-B-3-0104-C0-2-PLP1-500](#) [MLPS-B-3-0104-C0-2-PLP2-9MM](#) [MLPS-B-3-0105-C0-2-PLP1-750](#) [MLPS-B-3-0105-C0-2-PLP2-9MM](#) [MLPS-B-3-0106-C0-2-PLP2-10MM](#) [MLPS-B-3-0106-C0-2-PLPC3-9MM](#) [MLPS-B-3-0107-C0-4-PLP2-1000](#) [MLPS-B-3-0107-C0-4-PLP2-350](#) [MLPS-B-3-0108-C0-4-PLP2-350](#) [MLPS-B-3-0108-C0-4-PLP2-500](#) [MLPS-B-3-0108-C0-4-PLP2-9MM](#) [MLPS-B-3-0108-C0-4-PLPC3-188](#) [MLPS-B-3-0109-C0-4-PLP1-7MM](#) [MLPS-B-3-0109-C0-4-PLP2-9MM](#) [MLPS-B-3-0109-C0-4-PLPC3-188](#) [MLPS-B-3-0109-C0-4-PLPC3-7MM](#) [MLPS-B-3-0110-C0-4-PLP2-1000](#) [MLPS-B-3-0111-C0-4-PLP1-9MM](#) [MLPS-B-3-0111-C0-4-PLP2-250](#) [MLPS-B-3-0111-C0-4-PLP2-500](#) [MLPS-B-3-0112-C0-4-PLP1-200](#) [MLPS-B-3-0112-C0-4-PLP1-375](#) [MLPS-B-3-0112-C0-4-PLP2-350](#) [MLPS-B-3-0112-C0-4-PLP2-9MM](#) [MLPS-B-3-0113-C0-6-PLP1-460](#) [MLPS-B-3-0113-C0-6-PLP1-6MM](#) [MLPS-B-3-0113-C0-6-PLP2-7MM](#) [MLPS-B-3-0113-C0-6-PLP2-9MM](#) [MLPS-B-3-0113-C0-6-PLPC3-5MM](#) [MLPS-B-3-0201-CC-2-PLP1-188](#) [MLPS-B-3-0202-CC-2-PLP1-200](#) [MLPS-B-3-0202-CC-2-PLP2-9MM](#) [MLPS-B-3-0203-CC-2-PLP1-460](#) [MLPS-B-3-0203-CC-2-PLPC3-188](#) [MLPS-B-3-0204-CC-2-PLPC3-5MM](#) [MLPS-B-3-0206-CC-2-PLP2-500](#) [MLPS-B-3-0206-CC-2-PLP2-9MM](#) [MLPS-B-3-0207-CC-4-PLP1-460](#) [MLPS-B-3-0207-CC-4-PLP1-7MM](#) [MLPS-B-3-0207-CC-4-PLPC3-188](#) [MLPS-B-3-0207-CC-4-PLPC3-5MM](#) [MLPS-B-3-0208-CC-4-PLP1-6MM](#) [MLPS-B-3-0208-CC-4-PLP2-1000](#) [MLPS-B-3-0209-CC-4-PLP2-250](#) [MLPS-B-3-0210-CC-4-PLP1-200](#) [MLPS-B-3-0211-CC-4-PLP2-9MM](#) [MLPS-B-3-0211-CC-4-PLPC3-375](#) [MLPS-B-3-0212-CC-4-PLPC3-375](#) [MLPS-B-3-0213-CC-6-PLP1-8MM](#) [MLPS-B-3-0213-CC-6-PLP2-188](#) [MLPS-B-3-0214-CC-6-PLP1-188](#) [MLPS-B-3-0214-CC-6-PLP1-200](#) [MLPS-B-3-0214-CC-6-PLP1-350](#) [MLPS-B-3-0214-CC-6-PLP2-250](#) [MLPS-B-3-0301-CC-2-PLP1-375](#) [MLPS-B-3-0301-CC-2-PLP2-7MM](#) [MLPS-B-3-0302-CC-2-PLP1-5MM](#) [MLPS-B-3-0302-CC-2-PLP1-625](#) [MLPS-B-3-0302-CC-2-PLPC3-250](#) [MLPS-B-3-0303-CC-2-PLP1-8MM](#) [MLPS-B-3-0304-CC-2-PLP1-10MM](#) [MLPS-B-3-0304-CC-2-PLP1-188](#) [MLPS-B-3-0304-CC-2-PLP1-350](#) [MLPS-B-3-0304-CC-2-PLP2-6MM](#) [MLPS-B-3-0305-CC-4-PLP1-350](#) [MLPS-B-3-0305-CC-4-PLP1-6MM](#) [MLPS-B-3-0305-CC-4-PLP2-7MM](#)

[MLPS-B-3-0306-CC-4-PLP1-5MM](#) [MLPS-B-3-0306-CC-4-PLP1-8MM](#) [MLPS-B-3-0307-CC-4-PLP1-10MM](#) [MLPS-B-3-0307-CC-4-PLP1-188](#) [MLPS-B-3-0307-CC-4-PLP1-8MM](#) [MLPS-B-3-0308-CC-4-PLP1-313](#) [MLPS-B-3-0308-CC-4-PLP2-188](#) [MLPS-B-3-0309-CC-4-PLP1-625](#) [MLPS-B-3-0309-CC-4-PLP2-5MM](#) [MLPS-B-3-0309-CC-4-PLPC3-250](#) [MLPS-B-3-0310-CC-4-PLPC3-10MM](#) [MLPS-B-3-0310-CC-4-PLPC3-8MM](#)