






REV.	DESCRIPTION	DATE	APPROVED
G	Engineering Release.	04/29/14	M. C.
H	Updated Tolerance Block and Overall Width	08/01/14	J. C.
J	Engineering Update w/o Changes	05/13/16	J. C.



PART NO.	A ±.032 (.8)	B ±.016 (.4)	C ±.008 (.2)
UDD-200-C	2.0 (50.8)	1.0 (25.4)	-
UDD-250-C	2.5 (63.5)	1.5 (38.1)	-
UDD-300-C	3.0 (76.2)	2.0 (50.8)	-
UDD-350-C	3.5 (88.9)	2.5 (63.5)	-
UDD-400-C	4.0 (101.6)	3.0 (76.2)	-
UDD-450-C	4.5 (114.3)	3.5 (88.9)	-
UDD-500-C	5.0 (127.0)	4.0 (101.6)	-
UDD-550-C	5.5 (139.7)	4.5 (114.3)	-
UDD-600-C	6.0 (152.4)	5.0 (127.0)	-
UDD-650-C	6.5 (165.1)	5.5 (139.7)	-
UDD-700-C	7.0 (177.8)	6.0 (152.4)	-
UDD-750-C	7.5 (190.5)	6.5 (165.1)	-
UDD-800-C	8.0 (203.2)	7.0 (177.8)	-
UDD-850-C	8.5 (215.9)	7.5 (190.5)	3.75 (95.3)
UDD-900-C	9.0 (228.6)	8.0 (203.2)	4.00 (101.6)
UDD-950-C	9.5 (241.3)	8.5 (215.9)	4.25 (108.0)
UDD-1000-C	10.0 (254.0)	9.0 (228.6)	4.50 (114.3)
UDD-1050-C	10.5 (266.7)	9.5 (241.3)	4.75 (120.7)
UDD-1100-C	11.0 (279.4)	10.0 (254.0)	5.00 (127.0)



NOTE:

4. MATERIAL: NYLON 66, 15% GLASS, 94V-0, BLACK.
3. INTEGRATED S/S CLIPS PROVIDE GROUNDING CONTACT FROM PCB TO CHASSIS.
2. RECOMMENDED CARD THICKNESS 0.062" - 0.079" [1.6mm - 2.0mm].
1. RECOMMENDED PANEL THICKNESS 0.047" - 0.090" [1.2mm - 2.3mm].

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		 4 THOMAS, IRVINE, CA. 92618 TEL: (949) 951-8808 FAX: (949) 951-3974	
<u>DECIMALS</u>	<u>ANGULAR</u>		
.X ± .1	X° ± 1°		
.XX ± .01			
.XXX ± .005			
DESIGNED: T. Yin	DATE: 11/26/13	TITLE: UNIVERSAL NYLON CARD GUIDE W/ GROUNDING CLIP	
		PART NO: UDD-XXX-C	REVISION: J
CHECKED: B. Oliver	DATE: 11/26/13	CAGE CODE : 32559	SHEET # 1 OF 1
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

[UDD-200-C](#) [UDD-250-C](#) [UDD-300-C](#) [UDD-350-C](#) [UDD-400-C](#) [UDD-450-C](#) [UDD-500-C](#) [UDD-550-C](#) [UDD-600-C](#)
[UDD-650-C](#) [UDD-700-C](#) [UDD-750-C](#) [UDD-800-C](#) [UDD-850-C](#) [UDD-900-C](#) [UDD-950-C](#) [UDD-1000-C](#) [UDD-1050-C](#)
[UDD-1100-C](#)