

Full or partial part number

Home / LED Indication / Flexible Light Pipes / FLP System



Flexible Light Pipes, LED Indication

FLP System

Available Options:

Adapter LED Color/Wavelength

Amber/605nm

Adapter Optical Fiber Diameter

2mm

Lens Size

7.0mm

Lens Profile

Low Profile

Panel Cutout

Round

Luminous Intensity

300mcd

Optical Fiber Length

6.5 in.

Optical Fiber Color

Red



Part Number:

FR4-6.5-SA-F7P-2

Categories: FLEXIBLE LIGHT PIPES ,

LED INDICATION

Request Sample

Check Stock

Download Data Sheet

Download 3D Drawing

Download RoHS Docs

View List →

Additional information

Adapter LED Color/Wavelength	Amber/605nm, Amber/620nm, Blue/466nm, Blue/470nm, Green/563nm, Green/568nm, Green/570nm, Green568nm, N/A, Orange/620nm, Red 625nm / Green 568nm, Red 625nm/Green 568nm, Red 645nm / Green 568nm, Red/625nm, Red/640nm, Red/640nmnm, Red/645nm, Red/660nm, Turquoise/500nm, White/6000K, White/6500K, Yellow 585nm / Green 565nm, Yellow 585nm/Green 565nm, Yellow 590nm / Green 568nm, Yellow 590nm/Green 515nm, Yellow 590nm/Green 568nm, Yellow 590nm/Green568nm, Yellow/585nm, Yellow/588nm, Yellow/590nm
Adapter Optical Fiber Diameter	1mm, 2mm
Lens Size	3.2 x 6.4 mm, 3.2mm x 6.4mm, 4.0mm, 4.2mm, 5.1mm, 6.0mm IP67, 6.7mm x 4.2mm, 7.0mm, 9.0mm IP67, N/A
Lens Profile	Dome, Flat, Low Profile, Low Profile Diffused, Low Profile Fresnel, N/A
Panel Cutout	N/A, Oval, Rectangular, Round
Luminous Intensity	100mcd/60mcd, 120mcd, 15/5 mcd, 1500mcd, 15mcd/5mcd, 200mcd, 2200mcd, 250mcd, 300mcd, 350mcd, 400/80 mcd, 400mcd, 50mcd, 50mcd/50mcd, 6000mcd, 600mcd, 60mcd, 65mcd, 6mcd/8mcd, 70mcd, 800mcd, 8mcd/8mcd, 900mcd, N/A
Optical Fiber Length	1.0 in., 1.5 in., 10.0 in., 100.0 in., 118.0 in., 12.0 in., 12.3 in., 13.0 in., 14.0 in., 15.0 in., 18.0 in., 2.0 in., 2.1 in., 2.3 in., 2.5 iin., 2.5 in., 2.9 in., 24.0 in., 3.0 in., 3.25 in., 3.28 in., 3.5 in., 3.9 in., 36.0 in., 4.0 in., 4.1 in., 4.5 in., 5.0 in., 6.0 in., 6.5 in., 6.7 in., 8.0 in., 9.0 in., 9.5 in., N/A
Optical Fiber Color	Black, Blue, Green, N/A, Red, White, Yellow



Keep up with Bivar

Email*

Subscribe

- Products
- LED Indication
- Positioning Components
- Securing Circuit Cards
- Linear LED Lighting
- Smart Technology

- Solutions
- Engineered Solutions
- Industries
- Security & Surveillance
- Communication
- Industry 4.0

- Company
- Contact Us
- About Us
- How to Buy

BIVAR CORPORATE OFFICE

4 Thomas
Irvine, CA 92618

TEL: 800-767-3652
FAX: 949-951-3974

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

BIVAR:

FR4-6.5-SA-F7P-2