

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES AND ANGLES	TITLE	DWG NO.
ONE PLACE DECIMALS: $\pm .1$ [2.5]	THREE PLACE DECIMALS: $\pm .005$ [.127]		ANGLES $\pm 2^\circ$	LOW PROFILE SOCKET STRIP	CLH-1XX-XX-X-XX-XX
TWO PLACE DECIMALS: $\pm .01$ [.25]	FOUR PLACE DECIMALS: $\pm .0020$ [.0508]				SHEET 1 OF 2










TABLE 1		
ENTRY SPEC	CONTACT	INSULATOR
-DE (SEE FIG. 1)	C-73-03-X-X	CLH-XX-D
-DV (SEE FIG. 2)	C-73-01-X-X	CLH-XX-D
-TE (SEE FIG. 3)	C-73-02-X-X	CLH-XX-D
-PE (SEE FIG. 4)	C-73-04-X-X	CLH-XX-D
-BE (SEE FIG. 5)	C-73-01-X-X	CLH-XX-DBE



ENTRY SPECIFICATION STYLES
DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG. 1



"Q" = (# OF POS x .100) ± .005
"P" = ("Q" - .225/2) ± .020



AVAILABLE ON POSITIONS 03 THRU 50 ONLY

PROPRIETARY NOTE
THIS DRAWING IS THE PROPERTY OF SAMTEC CORPORATION. IT IS TO BE USED FOR THE MANUFACTURE OF SAMTEC PRODUCTS ONLY. IT IS NOT TO BE REPRODUCED, COPIED, OR DISTRIBUTED IN ANY MANNER WITHOUT THE WRITTEN PERMISSION OF SAMTEC CORPORATION.

MATERIAL: BODY: VICTRA E130 VICTRA E130 CONTACT: 521 PHOSPHOR BRONZE FULL HARD	 520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150 PHONE (812) 944-8733 P.O. BOX 1147 CODE 55322 MADE BY: PURVIS 10-4-94	DSGPROD/ASSEMBLY/100 CLH-ASM1 CLH-1XX-XX-X-XX-XX SHEET 1 OF 2
--	--	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[CLH-120-F-D-BE](#) [CLH-106-F-D-BE](#) [CLH-102-L-D-DV](#) [CLH-112-L-D-BE](#) [CLH-102-F-D-DV](#) [CLH-104-F-D-DV](#) [CLH-105-F-D-DV](#) [CLH-103-L-D-BE](#) [CLH-120-L-D-DV](#) [CLH-103-F-D-BE](#) [CLH-103-F-D-DV](#) [CLH-105-F-D-BE](#) [CLH-112-F-D-BE](#) [CLH-117-F-D-BE](#) [CLH-106-F-D-DV](#) [CLH-107-F-D-DV](#) [CLH-108-F-D-BE](#) [CLH-109-F-D-DV](#) [CLH-110-F-D-DV](#) [CLH-112-F-D-DV](#) [CLH-107-L-D-BE-A](#) [CLH-125-F-D-BE](#) [CLH-125-F-D-BE-A-K-TR](#) [CLH-115-F-D-BE](#) [CLH-104-F-D-BE](#) [CLH-111-F-D-BE](#) [CLH-150-L-D-DV](#) [CLH-114-F-D-BE](#) [CLH-110-F-D-BE](#) [CLH-107-F-D-BE](#) [CLH-113-F-D-BE](#) [CLH-102-F-D-BE](#) [CLH-109-F-D-BE](#) [CLH-128-F-D-BE](#) [CLH-150-L-D-BE](#) [CLH-116-F-D-BE](#)