





TFML-125-02-S-D



TFML-120-02-S-D



LOCKING HEADER TFML SERIES

SPECIFICATIONS

For complete specifications see www.samtec.com?TFML

Insulator Material:
Black Liquid Crystal Polymer



Terminal Material:
Phosphor Bronze

Current Rating:
2A @ 80°C ambient

Voltage Rating:
350 VAC mated with SFML

Operating Temp Range:
-65°C to +125°C


Plating:
Au over 50µ" (1.27µm) Ni

Locking Features:
10-20 = One Latch
25 & 30 = Two Latches
35-50 = Three Latches

Note:

Some sizes, styles and options are non-standard, non-returnable.

Mates with:
SFML




Processing:

Max Processing Temp:
230°C for 60 seconds


SMT Lead Coplanarity:
(0.10mm) .004" max (10-25)
(0.15mm) .006" max (30-50)

Suggested PCB Layouts:
For reference only. Please contact Samtec or go to www.samtec.com?TFML for recommended PCB layout.



TAPE & REEL AVAILABILITY

No tooling charges.
125 piece minimum order.
Order any quantity above minimum.
In-house design, manufacture.
Quick turn-around.
Call Samtec for specifications and ordering information.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 • Fax: 812-948-5047 SAMTEC UK • Tel: 01236 739292 • Fax: 01236 727113 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299
SAMTEC FRANCE • Tel: 01 60 95 06 60 • Fax: 01 60 95 06 61 SAMTEC ITALY • Tel: 39 039 6890337 • Fax: 39 039 6890315 SAMTEC ISRAEL • Tel: 972-3-7526600 • Fax: 972-3-7526690
SAMTEC SCANDINAVIA • Tel: +46-84477280 • Fax: +46-87420413 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 • Fax: 65 6841-1502 SAMTEC JAPAN • Tel: 81-424-42-8318 • Fax: 81-424-42-8319
SAMTEC CHINA • Tel: 86-21-5385-4089 • Fax: 86-21-5385-4047 SAMTEC TAIWAN • Tel: 886-02-2364-6077 • Fax: 886-02-2367-9531
SAMTEC HONG KONG • Tel: 852-26904858 • Fax: 852-26904842 SAMTEC ANZ • Tel: 613 9512 7747 • Fax: 613 9512 7745

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Samtec:](#)

[TFML-115-01-S-D-A-K](#)