



860L Series

Miniature-Size DIN Video Patch Cords



Product Description

New 860L Series Miniature-Size DIN Video Patch Cords feature a new miniature Patch Plug with a 0.200" dia. body and 0.035" dia. male center contact. Patch Cords are available in a variety of lengths and colors and mate to KINGS® new Miniature-Size DIN Video Jacks and Jackfields.



- 860L Series Miniature-Size DIN Video Patch Cords are made with Belden 1855A precision 75 Ohm video cable providing unsurpassed performance and reliability.



- Patch Cords feature molded black strain relief boots with a choice of 10 different cable jacket colors for signal identification and customization.



- Patch Cords are available in 10 standard lengths. Custom cord lengths are also available.
- 75 Ohm Miniature-Size Patch Plugs are made with precision machined components designed to provide long-term durability, reliability, and performance.

Specifications

Material


Body, Contact: Brass
 Ferrule: Commercial Bronze
 Insulators: Teflon®
 Cable Boot: Buna N Rubber
 Cable: Belden 1855A

Electrical

Impedance: 75 Ohms
 Frequency Range: DC – 3 GHz

Finishes

Body: Nickel over Copper
 Contacts: Gold over Nickel



860L-860-XXX01YY

Color
 Length "A" in inches
 Series Part Number

PART NUMBER	DIMA ± 1.25
860L-860-01201YY	12.00
860L-860-01801YY	18.00
860L-860-02401YY	24.00
860L-860-03601YY	36.00
860L-860-04801YY	48.00
860L-860-06001YY	60.00
860L-860-07201YY	72.00
860L-860-08401YY	84.00
860L-860-09601YY	96.00
860L-860-12001YY	120.00
860L-860-30001YY	300.00

YY	CABLE COLOR
-01	Brown
-02	Red
-03	Orange
-04	Yellow
-05	Green
-06	Blue
-07	Violet
-08	Grey
-09	White
-10	Black



Winchester Electronics
 199 Park Road Extension, Suite 104
 Middlebury, Connecticut 06762
 203.741.5400 Phone
 203.741.5500 Fax
www.winchesterelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[860L-860-0120110](#) [860L-860-0240110](#) [860L-860-0360110](#) [860L-860-0480110](#) [860L-860-0600110](#) [860L-860-0720110](#) [860L-860-0840110](#) [860L-860-0960110](#) [860L-860-1200110](#) [860L-860-3000110](#)