

Indicator Lights

To match 8500, 8600, R13, 1500, 1550, 5500, 8300 and 7000 switches

Colours and voltages:

Neon

Available with Red, Amber, Green or Clear lenses
100/130V (marked 110V), 200/250V (marked 230V)

Filament lamp

Available with Red, Amber or Green lenses
6V, 12/14V, 24/28V

To create a catalogue number:

Refer to the 2 columns below (terminal and type), then state: Lens colour, voltage and whether neon or filament lamp.

- ▶ Indicator lights
- ▶ Neon or filament lamp
- ▶ Bezel sizes from 6.7 to 16.3mm diameter
- ▶ Red, amber green and clear neons
- ▶ Red, amber and green filament lamps
- ▶ Styles to match rocker and push switches

▶ TERM	▶ TYPE	ILLUM'N OPTIONS	APPROVAL	
H 4.8			   	   
H 4.8			   	   
T				
X				
H 4.8			  	  
		Approvals details - contact sales		
C 6.3			   	   
H 4.8				
K 2.8				
T				
U				
C 6.3			   	   
H 4.8				
K 2.8				
T				
U				
C 6.3			  	  
H 4.8				

Full product details on pages 12-13					Cut-out		Flange	
Body Code	Panel thickness	Cut-out						
B	0.75-1.25	19.1/19.2	12.9/13.0					
	1.25-2.0	19.3/19.4	12.9/13.0					
	2.0-3.0	19.7/19.8	12.9/13.0					
Full product details on pages 14-15					Cut-out		Flange	
Body Code	Panel thickness	Cut-out						
B	0.75-1.25	19.1/19.2	12.9/13.0					
	1.25-2.0	19.3/19.4	12.9/13.0					
	2.0-3.0	19.7/19.8	12.9/13.0					
Full product details on pages 33					Cut-out		Flange	
Snap fixing in panels thickness up to 3.0								
Full product details on pages 22-23					Cut-out		Flange	
Body Code	Cut-out		Flange					
	Y	X	Y	X				
A	12.2/12.3	27.2/27.3	14.0	30.2				
B	11.0/11.1	30.0/30.1	14.0	33.4				
L	11.0/11.1	30.0/30.1	14.0	31.9				
R	14.0/14.1	28.5/28.6	17.0	31.5				
T	11.5/11.6	28.2/28.3	14.0	30.2				
Full product details on pages 28-29					Cut-out		Flange	
Body Code	Cut-out		Flange					
	Y	X	Y	X				
A	22.3/22.4	27.2/27.3	25.0	30.2				
B	22.1/22.2	30.0/30.1	25.0	33.4				
L	22.1/22.2	30.0/30.1	25.0	32.0				
R	23.0/25.4	28.4/28.5	28.9	33.2				
T	22.3/22.4	28.2/28.3	25.0	30.2				
Full product details on pages 44-45					Cut-out		Flange	
Body Code	Cut-out		Flange					
H	Ø25.0/25.2		Ø28.0					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bulgin:

C058900NAA