

R13 Round Rocker Switches 10A 250Vac



- ▶ Miniature round rocker switch
- ▶ Ratings up to 10A, 250Vac
- ▶ Single & double pole
- ▶ Illuminated & non-illuminated, neon and LED
- ▶ Choice of actuators
- ▶ Matching indicator
- ▶ Panel cut out: 20.2 dia.

Approvals and specifications



SP 10(4)A 250Vac T85 1E4



DP 10(4)A 250Vac T85 1E4



UL CSA SP 16A 125Vac & 10A 250Vac
UL CSA DP 16A 125Vac, 10A 250Vac, 10A 28Vdc
UL 85°C, file E67774(S), CSA file LR45128

RoHS compliant

Single pole has μ contact gap. Technical data on pages 4 & 5.

Special products

Are made to order and can be supplied with a range of body and rocker/lens colours, print & lamp voltage.
Call sales for availability to your special requirements.

R13 112A AAA

TERMINAL FUNCTION ROCKER BODY PRINT, COLOUR, VOLTAGE ETC

PRODUCT DETAILS




SP ON - OFF μ

Cat no.
R13 112A AAA




SP ON - OFF μ

Cat no.
R13 112A AAB



SP ON - OFF μ
Lit 230V

Cat no.
R13 112B NAA




SP ON - OFF μ
Lit 230V

Cat no.
R13 112B NAB




DP ON - OFF

Cat no.
R13 244A AAA



SP ON - OFF μ
Lit 230V

Cat no.
R13 112B NAC



SP ON - ON μ

Cat no.
R13 112C AAA



SP ON - OFF - ON μ

Cat no.
R13 112D AAA



SP ON - OFF μ
(Momentary ON)

Cat no.
R13 208F AAA*




DP ON - OFF
Lit 230V

Cat no.
R13 244B NAA


DIMENSIONS (mm)

Panel cut-out




Snap fixing into panel thickness up to 3.0

Single pole



* R13 208F has 12.5mm deep body

Double pole





R13 112B NAA



R13 112A AAA



R13 112A2 ---

PRODUCT DETAILS



SP ON - OFF μ
Bright colour ON signal

Cat no.

R13 112A2 - -



SP ON - OFF μ
Lit Window

Cat no.


R13 112B2 - -



SP ON - OFF μ
Paddle tip has red LED

Cat no.





R13 112LP - -




Indicator light

Cat no.


R9 92B - - -



PANEL CUT-OUT (mm)



Snap fixing into
2.0 to 3.0mm panels



Snap fixing into
0.7 to 3.0mm panels



Protective cover L188

Snap on to bodies (not R13 211 or R13 112LP), this reduces maximum acceptable panel thickness by 0.8mm.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bulgin:

F0188LOAAA