


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

1	2	3	4	5
Item No.	Part No.	Description		
1	See Table 1	SR Connector		
2	UL1571, 30 AWG	Black		
<u>Electrical Specifications</u>				
Current: 0.7A DC				
Voltage: 50V DC				

TABLE 1				
ITEM	NUMBER OF CIRCUITS	CONNECTOR PART NO.	ASSEMBLY PART NO.	TOTAL WIRE REQUIRED
1	2	02SR-3S	A02SR02SR30K102A	218 mm
1	3	03SR-3S	A03SR03SR30K102A	326 mm
1	4	04SR-3S	A04SR04SR30K102A	435 mm
1	5	05SR-3S	A05SR05SR30K102A	544 mm
1	6	06SR-3S	A06SR06SR30K102A	653 mm
1	7	07SR-3S	A07SR07SR30K102A	762 mm
1	8	08SR-3S	A08SR08SR30K102A	870 mm
1	9	09SR-3S	A09SR09SR30K102A	979 mm
1	10	10SR-3S	A10SR10SR30K102A	1,088 mm
1	11	11SR-3S	A11SR11SR30K102A	1,197 mm
1	12	12SR-3S	A12SR12SR30K102A	1,306 mm
1	13	13SR-3S	A13SR13SR30K102A	1,414 mm
1	14	14SR-3S	A14SR14SR30K102A	1,523 mm



ZONE	REV	DESCRIPTION	DATE	APPROVED
	1	Add Electrical Specifications	6/29/2018	LM

All dimensions are in millimeters with a default tolerance of +/- 5.0 unless otherwise specified.					CUSTOMER NAME					
					DESCRIPTION					
					1.0mm Pitch SR Standard Catalog Assembly - 4" Overall Length - Pin Out: 1 to 1					
Drawn By: Larissa Mosley Checked By: Steven Pilkington					SIZE	CUSTOMER PART NO.	PART NO.	REV		
					SEE TABLE 1					
					SCALE	1:1	DRAWING NO. GAM-286	DATE 4/10/2018		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[A08SR08SR30K102A](#) [A02SR02SR30K102A](#) [A05SR05SR30K102A](#) [A09SR09SR30K102A](#) [A03SR03SR30K102A](#)  
[A10SR10SR30K102A](#) [A06SR06SR30K102A](#) [A11KR11KR26E305B](#) [A12KR12KR26E305B](#) [A04SR04SR30K102A](#)  
[A14KR14KR26E305B](#) [A13KR13KR26E305B](#) [A07SR07SR30K102A](#)