

QL 4 SAKA10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	SAK Series, Cross-connector, Cross-connector, Number of poles: 4
Order No.	0135700000
Type	QL 4 SAKA10
GTIN (EAN)	4008190118822
Qty.	50 pc(s).

QL 4 SAKA10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	2 mm	Depth (inches)	0.079 inch
Height	6 mm	Height (inches)	0.236 inch
Width	43.7 mm	Width (inches)	1.72 inch
Net weight	3.46 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Environmental Product Compliance

REACH SVHC	SCIP	86596b21-b817-43a9-8e4c-ac00e41b9a24
Lead 7439-92-1		

Material data

Material	Cu Zn	Colour	grey
----------	-------	--------	------

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in	Type of mounting	when screwed in

Cross-connector

Number of cross-connected terminals	4	Rated current, 2-pole	47 A
Rated current, multi-pole	36 A	Type	Cross-connector

Dimensions

Pitch in mm (P)	12 mm
-----------------	-------

General

Installation advice	Direct mounting	Number of poles	4
---------------------	-----------------	-----------------	---

Rating data

Rated current	36 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

Approvals

ROHS	Conform
------	---------

Creation date September 15, 2022 7:30:45 PM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

QL 4 SAKA10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0135700000](#)