

Q 10 SAK2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 10
Order No.	0368700000
Type	Q 10 SAK2.5
GTIN (EAN)	4008190107796
Qty.	20 pc(s).

Q 10 SAK2.5**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	20.5 mm	Depth (inches)	0.807 inch
Height	6 mm	Height (inches)	0.236 inch
Width	60.6 mm	Width (inches)	2.386 inch
Net weight	17.5 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	CuSn	Colour	grey
----------	------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	10	Rated current, 2-pole	41 A
Rated current, multi-pole	41 A	Type	Cross-connector

Dimensions

Pitch in mm (P)	6 mm
-----------------	------

General

Installation advice	Direct mounting	Number of poles	10
---------------------	-----------------	-----------------	----

Rating data

Rated current	24 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40		

Approvals

Approvals



ROHS	Conform
------	---------

Q 10 SAK2.5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of Conformity	EAC certificate
Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0368700000](#)