

QB 58/8/9/WI**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Version	SAK Series, Cross-connector, for cross-connection link, Number of poles: 58
Order No.	0545300000
Type	QB 58/8/9/WI
GTIN (EAN)	4008190125080
Qty.	10 pc(s).

QB 58/8/9/WI

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	17.5 mm	Depth (inches)	0.689 inch
Height	458.5 mm	Height (inches)	18.051 inch
Width	0.8 mm	Width (inches)	0.031 inch
Net weight	22.1 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-60 °C.../TX]130 °C
---------------------	----------------	-----------------------	---------------------

Material data

Material	Copper	Colour	grey
----------	--------	--------	------

System specifications

Version	for cross-connection link
---------	---------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	when screwed in		

Cross-connector

Number of cross-connected terminals	58	Type	Cross-connector
-------------------------------------	----	------	-----------------

Dimensions

Pitch in mm (P)	8 mm
-----------------	------

General

Installation advice	Direct mounting	Number of poles	58
---------------------	-----------------	-----------------	----

Rating data

Rated current	27 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40		

Approvals

Approvals



ROHS	Conform
------	---------

Technical data

Downloads

Approval/Certificate/Document of Conformity	EAC certificate
Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

QB 58/8/9/WI

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Insulation profiles



General ordering data

Type	ISPF QB58 BL	Version
Order No.	0546080000	Accessories, Insulation profile
GTIN (EAN)	4008190927035	
Qty.	10 pc(s).	
Type	ISPF QB58 RT	Version
Order No.	0546040000	Accessories, Insulation profile
GTIN (EAN)	4008190497941	
Qty.	10 pc(s).	
Type	ISPF QB58 SW	Version
Order No.	0546000000	Accessories, Insulation profile
GTIN (EAN)	4008190116705	
Qty.	10 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0545300000](#)