

**Q 10 AKZ1.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

**General ordering data**

|            |                                                                             |
|------------|-----------------------------------------------------------------------------|
| Version    | SAK Series, Cross-connector, for cross-connection link, Number of poles: 10 |
| Order No.  | <a href="#">0368500000</a>                                                  |
| Type       | Q 10 AKZ1.5                                                                 |
| GTIN (EAN) | 4008190159481                                                               |
| Qty.       | 20 pc(s).                                                                   |

**Q 10 AKZ1.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 11 mm   | Depth (inches)  | 0.433 inch |
| Height     | 4 mm    | Height (inches) | 0.157 inch |
| Width      | 49.9 mm | Width (inches)  | 1.965 inch |
| Net weight | 9.15 g  |                 |            |

**Temperatures**

|                     |                |
|---------------------|----------------|
| Storage temperature | -25 °C...55 °C |
|---------------------|----------------|

**Environmental Product Compliance**

|            |                |
|------------|----------------|
| REACH SVHC | Lead 7439-92-1 |
|------------|----------------|

**Material data**

|          |       |        |      |
|----------|-------|--------|------|
| Material | Cu Zn | Colour | grey |
|----------|-------|--------|------|

**System specifications**

|         |                           |
|---------|---------------------------|
| Version | for cross-connection link |
|---------|---------------------------|

**Additional technical data**

|                          |                 |                     |                 |
|--------------------------|-----------------|---------------------|-----------------|
| Explosion-tested version | No              | Installation advice | Direct mounting |
| Type of fixing           | when screwed in |                     |                 |

**Cross-connector**

|                                     |                 |                           |      |
|-------------------------------------|-----------------|---------------------------|------|
| Number of cross-connected terminals | 10              | Rated current, multi-pole | 24 A |
| Type                                | Cross-connector |                           |      |

**Dimensions**

|                 |        |
|-----------------|--------|
| Pitch in mm (P) | 5.1 mm |
|-----------------|--------|

**General**

|                     |                 |                 |    |
|---------------------|-----------------|-----------------|----|
| Installation advice | Direct mounting | Number of poles | 10 |
|---------------------|-----------------|-----------------|----|

**Rating data**

|               |      |
|---------------|------|
| Rated current | 24 A |
|---------------|------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ECLASS 9.0  | 27-14-11-40 |
| ECLASS 9.1  | 27-14-11-40 | ECLASS 10.0 | 27-14-11-40 |
| ECLASS 11.0 | 27-14-11-40 |             |             |

## Q 10 AKZ1.5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Approvals

Approvals



ROHS

Conform

### Downloads

Approval/Certificate/Document of  
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[EPLAN, WSCAD, Zuken E3.S](#)

User Documentation

[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[0368500000](#)