

**HDC MBUS4 D5E MC****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

**General ordering data**

Version

Order No. [2427920000](#)

Type HDC MBUS4 D5E MC

GTIN (EAN) 4050118437119

Qty. 2 pc(s).

Creation date September 17, 2022 10:14:01 PM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

## HDC MBUS4 D5E MC

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Height	34.8 mm	Height (inches)	1.37 inch
Width	12.2 mm	Width (inches)	0.48 inch
Net weight	8 g		

### Temperatures

Limit temperature	-40 °C ... 90 °C
-------------------	------------------

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1	SCIP	2ac5c63f-7f5e-465a-860d-49cfb7bbe
------------	----------------	------	-----------------------------------

### General data

Category	Cat. 5e	Coding	D
Contact surface	Gold-plated	Insulation strength	≥ 100 MΩ
Number of poles	4	Plugging cycles	100
Pollution severity	2	Rated current	4 A
Rated voltage	250 V	Transmission rate	100 MBit/s
Type	Pin		

### Classifications

ETIM 6.0	EC002312	ETIM 7.0	EC002312
ETIM 8.0	EC002312	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-02-18	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-92	ECLASS 12.0	27-44-02-92

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">EPLAN</a>
Product Change Notification	<a href="#">PCN</a> <a href="#">PCN</a>
User Documentation	<a href="#">Instructions sheet HDC ModuPlug field attachable</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2427920000](#)