

HDC XX5E02 FMSRJ45-0500**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

General ordering data

Version	
Order No.	2503720500
Type	HDC XX5E02 FMSRJ45-0500
GTIN (EAN)	4050118523430
Qty.	1 pc(s).

HDC XX5E02 FMSRJ45-0500

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	0.001 g
------------	---------

Temperatures

Limit temperature	-40 °C ... 90 °C
-------------------	------------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1	SCIP	2ac5c63f-7f5e-465a-860d-49cfb7bbe
------------	----------------	------	-----------------------------------

General data

Cable length	5 m	Category	Cat. 5e
Coding	D	Contact surface	Au (Gold)
Insulation strength	$\geq 10^8 \Omega$	Module side version	Female
Number of poles	4	Opposite side version	Male, straight, RJ45
Pollution severity	2	Rated current	4 A
Rated voltage	250 V	Transmission rate	100 MBit/s

Cable technical specifications

Cable length	5 m	
Colour coding	white, yellow, blue, orange	
Halogen	Yes, No	
Outside diameter	7.25 mm $\pm$ 0.3	
Outside diameter	Diameter	7.25 mm
	Signs	$\pm$
	Tolerance	0.3
Sheath material	Radox EM 104	
Sheathing colour	blue	
Shielded	Yes	

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ECLASS 9.0	27-06-03-07
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-07
ECLASS 11.0	27-06-03-07	ECLASS 12.0	27-06-03-07

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

HDC XX5E02 FMSRJ45-0500

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

RJ45		M12
1	yellow	1
3	white	2
2	orange	3
6	blue	4

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2503720500](#)