

THM MULTIMARK PLUS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Version	Marking systems, Thermotransfer printer, Thermotransfer, 300 DPI, MultiMark, Shrink-fit sleeves, Label reel
Order No.	2599440000
Type	THM MULTIMARK PLUS
GTIN (EAN)	4050118626360
Qty.	1 pc(s).

THM MULTIMARK PLUS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	274 mm	Depth (inches)	10.787 inch
Height	446 mm	Height (inches)	17.559 inch
Width	242 mm	Width (inches)	9.528 inch
Net weight	10,000 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Labelling systems

Included in delivery	THM MultiMark, USB cable, Mains cable, Euro plug, US plug, UK plug, Printer driver, Software M-Print® PRO, RIBBON MM-TB 25/360 SW ink ribbon, RIBBON MM 110/360 SW ink ribbon, Ink ribbon core, Print roller, Pressure roller, Manual, W-LAN stick	Interface	
Marker type	MultiMark, Shrink-fit sleeves, Label reel	Operating system	USB 2.0, Ethernet, Wi-Fi Windows 7, Windows 8, Windows 8.1, Windows 10
Operation with rechargeable batteries	No	Print resolution, max.	300 DPI
Printing method	Thermotransfer	Printing speed	max. 300 mm/s
Software	M-Print® PRO	System requirements	PC with operating system Windows 7, 8 or 10
Voltage supply	100...240 V AC		

Classifications

ETIM 6.0	EC000610	ETIM 7.0	EC000610
ETIM 8.0	EC000610	ECLASS 9.0	24-32-11-90
ECLASS 9.1	24-32-11-02	ECLASS 10.0	24-32-11-90
ECLASS 11.0	24-32-11-90	ECLASS 12.0	24-32-11-90

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	China RoHS Declaration Declaration of Conformity
User Documentation	MANUAL THM MULTIMARK PLUS
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2599440000](#)