

HDC 06B ALU EMC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The new Weidmüller RockStar® IP65 EMV enclosures are ideally suited for use in the harshest environmental conditions and provide protection against electromagnetic interference. A heavy-duty connector consists of a connector insert and its protective housing. The new plastic straps are easy to lock and can be replaced at any time. All Weidmüller RockStar® enclosures are made of high quality die-cast aluminium. This makes them impact- and corrosion-resistant, yet compact and lightweight.

General ordering data

Version	HDC enclosures, Size: 3, Protection degree: IP65 (in plugged condition), Bulkhead housing, End-locking clamp, lower side, End-locking clamp replaceable
Order No.	2542230000
Type	HDC 06B ALU EMC
GTIN (EAN)	4050118648720
Qty.	1 pc(s).

Creation date September 17, 2022 11:52:56 PM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

HDC 06B ALU EMC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	80 mm	Depth (inches)	3.15 inch
Height	30 mm	Height (inches)	1.181 inch
Width	45 mm	Width (inches)	1.772 inch
Net weight	88 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Environmental Product Compliance

Chemical resistance	Substance	Hydraulic oil
	Chemical resistance	Resistant
	Substance	Petrol
	Chemical resistance	Resistant
	Substance	UV
	Chemical resistance	Resistant
	Substance	Ozone
	Chemical resistance	Resistant

General data

EMC housings	Yes	Housing main material	diecast aluminium
Material of locking element	PA 66/6, Stainless steel, rust-proof	Protection degree	IP65 (in plugged condition)
Surface finish	Powder coating	UL 94 flammability rating	V-0

Version

BG	3	Clamp version	End-locking clamp
Cover	without cover	Design of housing	Bulkhead housing
Design of locking system	End-locking clamp, lower side, End-locking clamp replaceable	Sealing	
Size	3		FPM
Top part/bottom part/lid	lower part	Suitable for ModuPlug®	Yes
		Type	Bulkhead (feed-through)

Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ECLASS 9.0	27-44-02-02
ECLASS 9.1	27-44-02-02	ECLASS 10.0	27-44-02-02
ECLASS 11.0	27-44-02-02	ECLASS 12.0	27-44-02-02

Approvals

Approvals



UL File Number Search	UL Website
Certificate No. (cURus)	E92202

HDC 06B ALU EMC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads


Engineering Data	CAD data – STEP
Engineering Data	EPLAN
Product Change Notification	20220214 Technical change to HDC housings 20220214 Technische Änderung bei HDC-Gehäusen
Catalogues	Catalogues in PDF-format

HDC 06B ALU EMC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2542230000](#)