

**THM MT30X 20/10 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The THM labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system under Windows optimise every marking effort.

- High-quality polyester labels in various colours or inexpensive paper labels are available
- Labels are automatically positioned in the printer for perfectly centred prints on each label.

**General ordering data**

|                    |                                                       |
|--------------------|-------------------------------------------------------|
| Version            | THM, Device markers, 10 x 20 mm, white                |
| Order No.          | <a href="#">2556240000</a>                            |
| Type               | THM MT30X 20/10 WS                                    |
| GTIN (EAN)         | 4050118567625                                         |
| Qty.               | 10,000 pc(s).                                         |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a> |

## THM MT30X 20/10 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Height     | 10 mm   | Height (inches) | 0.394 inch |
| Width      | 20 mm   | Width (inches)  | 0.787 inch |
| Net weight | 0.038 g |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

## General data

|                                   |                             |                                   |                               |
|-----------------------------------|-----------------------------|-----------------------------------|-------------------------------|
| Adhesive                          | Acrylate adhesive           | Approval acc. to UL 969           | Yes                           |
| Colour                            | white                       | Halogen                           | No                            |
| Material                          | Polyester                   | Number of markers per combination | 1 Label reel = Device markers |
| Number per roll                   | 10,000                      | Operating temperature range       | -40...150 °C                  |
| Operating temperature range, max. | 150 °C                      | Operating temperature range, min. | -40 °C                        |
| Printing method                   | Thermal transfer            | UL 94 flammability rating         | V-0                           |
| Version                           | Self-adhesive, halogen-free | Width                             | 20 mm                         |

## Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|

### THM MT30X 20/10 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2556240000](#)