

THM MULTIMARK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Version	Marking systems, Thermotransfer printer, Thermotransfer, 300 DPI, MultiMark, Shrink-fit sleeves, Label reel
Order No.	2599430000
Type	THM MULTIMARK
GTIN (EAN)	4050118626377
Qty.	1 pc(s).

Creation date September 18, 2022 12:41:29 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

THM MULTIMARK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	253 mm	Depth (inches)	9.961 inch
Height	320 mm	Height (inches)	12.598 inch
Width	253 mm	Width (inches)	9.961 inch
Net weight	5,800 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Labelling systems

Included in delivery	THM MultiMark, Manual, USB cable, Mains cable, Euro plug, US plug, UK plug, Printer driver, Software M-Print® PRO, RIBBON MM-TB 25/360 SW ink ribbon, RIBBON MM 110/360 SW ink ribbon, Ink ribbon core, Print roller, Pressure roller	Interface	USB 2.0, Ethernet
Marker type	MultiMark, Shrink-fit sleeves, Label reel	Memory (RAM)	256 MB
Operating system	Windows 7, Windows 8, Windows 8.1, Windows 10	Operation with rechargeable batteries	No
Print resolution, max.	300 DPI	Printing method	Thermotransfer
Printing speed	max. 150 mm/s	Software	M-Print® PRO
System requirements	PC with operating system Windows 7, 8 or 10	Voltage supply	100...240 V AC

Classifications

ETIM 6.0	EC000610	ETIM 7.0	EC000610
ETIM 8.0	EC000610	ECLASS 9.0	24-32-11-90
ECLASS 9.1	24-32-11-02	ECLASS 10.0	24-32-11-90
ECLASS 11.0	24-32-11-90	ECLASS 12.0	24-32-11-90

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity	China RoHS Declaration Declaration of Conformity
User Documentation	THM MULTIMARK
Catalogues	Catalogues in PDF-format

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2599430000](#)