

**ZQV 6N/6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Order No.  | <a href="#">2733950000</a> |
| Type       | ZQV 6N/6                   |
| GTIN (EAN) | 4064675066699              |
| Qty.       | 20 pc(s).                  |

**ZQV 6N/6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |        |
|------------|--------|
| Net weight | 8.51 g |
|------------|--------|

**Temperatures**

|                     |                |                       |                     |
|---------------------|----------------|-----------------------|---------------------|
| Storage temperature | -25 °C...55 °C | Operating temperature | -60 °C.../TX]130 °C |
|---------------------|----------------|-----------------------|---------------------|

**Material data**

|                           |       |        |        |
|---------------------------|-------|--------|--------|
| Material                  | Wemid | Colour | orange |
| UL 94 flammability rating | V-0   |        |        |

**Additional technical data**

|                |         |
|----------------|---------|
| Type of fixing | Plugged |
|----------------|---------|

**Cross-connector**

|                           |      |
|---------------------------|------|
| Rated current, multi-pole | 41 A |
|---------------------------|------|

**Dimensions**

|                 |      |
|-----------------|------|
| Pitch in mm (P) | 8 mm |
|-----------------|------|

**General**

|                 |   |
|-----------------|---|
| Number of poles | 6 |
|-----------------|---|

**Rating data**

|               |      |
|---------------|------|
| Rated current | 41 A |
|---------------|------|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000489    | ETIM 7.0    | EC000489    |
| ETIM 8.0    | EC000489    | ECLASS 9.0  | 27-14-11-40 |
| ECLASS 9.1  | 27-14-11-40 | ECLASS 10.0 | 27-14-11-40 |
| ECLASS 11.0 | 27-14-11-40 | ECLASS 12.0 | 27-14-11-40 |

**Downloads**

|                    |                                          |
|--------------------|------------------------------------------|
| Engineering Data   | <a href="#">CAD data – STEP</a>          |
| Engineering Data   | <a href="#">EPLAN</a>                    |
| User Documentation | <a href="#">BPZL ZQV 2.5</a>             |
| Catalogues         | <a href="#">Catalogues in PDF-format</a> |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[2733950000](#)