

PAC-S300-SD25-V6-4M**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm² or 0.25 mm².
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

General ordering data

Version	Pre-assembled cable, PAC, Cable LiYCY, 0.25 mm ²
Order No.	7789845040
Type	PAC-S300-SD25-V6-4M
GTIN (EAN)	4032248302109
Qty.	1 pc(s).

PAC-S300-SD25-V6-4M

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight 802 g

Temperatures

Storage temperature -10...60 °C

Operating temperature -10...50 °C

Environmental Product Compliance

REACH SVHC

Lead 7439-92-1

SCIP

4bbf2c0d-0764-4fc8-bb24-9351c28c190d

General Data

Cable	Cable LiYCY
Connector PLC side	SIEMENS S7300 6ES7921-3AH20-1AA0 40P
Material	PVC
Outer diameter	10.15 ± 1 mm
Wire cross-section	0.25 mm ²

Cable length	4 m
Interface connector	SUB-D FEMALE 25P
Number of poles, min.	25-pole
Suitable for	Analogue signals

Electrical Data

Capacity wire / shield	300 pF/m
High voltage test	1 kV/1s
Rated voltage	≤ 60 Vdc ≤ 25 Vac
Total current, max.	3 A

Capacity wire / wires	300 pF/m
Permissible current strength per path, max.	1 A
Resistance	≤ 80 mΩ/m

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20	ECLASS 12.0	27-24-22-20

Approvals

ROHS Conform

DownloadsCatalogues [Catalogues in PDF-format](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7789845040](#)