

SIHA 3/G20/LD 10-36V**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Product image

The fuse holder SIHA quickly turns a disconnect terminal into a fuse terminal: simply remove the disconnect lever and attach the fuse unit.

General ordering data

Version	Accessories, Fuse holder, Rated cross-section: Plug-in connection, Wemid, dark beige, Operating instructions/catalogue
Order No.	7921570000
Type	SIHA 3/G20/LD 10-36V
GTIN (EAN)	4032248322503
Qty.	25 pc(s).

SIHA 3/G20/LD 10-36V

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Depth	63.1 mm	Depth (inches)	2.484 inch
Height	39.38 mm	Height (inches)	1.55 inch
Width	6 mm	Width (inches)	0.236 inch
Net weight	8.28 g		

Temperatures

Operating temperature	-50 °C.../TX]120 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Insulating material	Wemid
Colour	black	UL 94 flammability rating	V-0

System specifications

Version	Fuse cartridge	End cover plate required	No
---------	----------------	--------------------------	----

Additional technical data

Installation advice	Operating instructions/ catalogue	Type of mounting	Plugged
---------------------	--------------------------------------	------------------	---------

Conductors for clamping (rated connection)

Type of connection	Plug-in connection
--------------------	--------------------

General

Installation advice	Operating instructions/ catalogue	Operating temperature range, max.	120 °C
---------------------	--------------------------------------	-----------------------------------	--------

Rating data

Rated voltage	250 V	Rated impulse withstand voltage	4 kV
Pollution severity	3		

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

Approvals

ROHS	Conform
------	---------

SIHA 3/G20/LD 10-36V

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

Technical data

info@weidmueller.com

www.weidmueller.com

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD, Zuken E3.S
Product Change Notification	PCN - EN PCN - DE
User Documentation	Beipackzettel_SIHA3.pdf StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format
Brochures	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[7921570000](#)