

## IE-BP-V14P

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



For protecting your devices against dust and dirt.

### General ordering data

|            |                                        |
|------------|----------------------------------------|
| Version    | Flange-mounted housing, protective cap |
| Order No.  | <a href="#">1058310000</a>             |
| Type       | IE-BP-V14P                             |
| GTIN (EAN) | 4032248799404                          |
| Qty.       | 10 pc(s).                              |

**IE-BP-V14P****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |                |            |
|------------|---------|----------------|------------|
| Depth      | 22.9 mm | Depth (inches) | 0.902 inch |
| Net weight | 4.778 g |                |            |

**Temperatures**

|                       |                |
|-----------------------|----------------|
| Operating temperature | -40 °C...70 °C |
|-----------------------|----------------|

**General data**

|                           |       |                       |              |
|---------------------------|-------|-----------------------|--------------|
| Colour                    | black | Housing main material | PA UL 94 V0  |
| Protection degree         | IP67  | Type of mounting      | Indoors only |
| UL 94 flammability rating | V-0   |                       |              |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002314    | ETIM 7.0    | EC002314    |
| ETIM 8.0    | EC002314    | ECLASS 9.0  | 27-44-02-08 |
| ECLASS 9.1  | 27-44-02-08 | ECLASS 10.0 | 27-44-02-08 |
| ECLASS 11.0 | 27-44-02-08 |             |             |

**Approvals**

Approvals



|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|                    |                                                                                                                       |
|--------------------|-----------------------------------------------------------------------------------------------------------------------|
| Engineering Data   | <a href="#">EPLAN, WSCAD, Zuken E3.S</a>                                                                              |
| User Documentation | <a href="#">MAN IE GUIDE DE</a><br><a href="#">MAN IE GUIDE EN</a>                                                    |
| Catalogues         | <a href="#">Catalogues in PDF-format</a>                                                                              |
| Brochures          | <a href="#">FL FIELDWIRING EN</a><br><a href="#">PI PROFINET CABLING EN</a><br><a href="#">PI PROFINET CABLING EN</a> |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1058310000](#)