

M-D-STRIPAX AWG 20+22**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

- Flexible and solid wire with PVC, Teflon (PTFE) and silicone insulation
- No damage to the wire thanks to specially shaped blade
- No splicing of individual wires
- Blade inserts are easy to replace
- All inserts fit one housing
- Guide bars in the blade cassettes facilitate correct positioning of the wire in the tool

General ordering data

Version	Tools, Stripping and cutting tool
Order No.	9003730000
Type	M-D-STRIPAX AWG 20+22
GTIN (EAN)	4008190102012
Qty.	1 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2022-03-01
Alternative product	9003630000

Creation date September 18, 2022 4:16:40 AM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

M-D-STRIPAX AWG 20+22**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	16 mm	Depth (inches)	0.63 inch
Height	135 mm	Height (inches)	5.315 inch
Width	82 mm	Width (inches)	3.228 inch
Net weight	96.28 g		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1	SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141
------------	----------------	------	--------------------------------------

Technical data

Description of article	Stripping tool for up to AWG 20, for PTFE
------------------------	---

Stripping tools

Cable type	Conductor with custom insulation	Max. conductor diameter	0.92 mm
Min. conductor diameter	0.88 mm	Stripping length, max.	7 mm
Stripping range AWG, max.	20 AWG	Stripping range AWG, min.	20 AWG

Classifications

ETIM 6.0	EC002109	ETIM 7.0	EC002109
ETIM 8.0	EC002109	ECLASS 9.0	21-04-37-06
ECLASS 9.1	21-04-37-06	ECLASS 10.0	21-04-37-06
ECLASS 11.0	21-04-37-06	ECLASS 12.0	21-04-37-06

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

M-D-STRIPAX AWG 20+22

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[9003730000](#)