

THM GEW 18/9 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM GEW woven-fabric labels are made from a very flexible cotton fabric. Delivery on reels for use with thermal transfer printers enables an adhesive layer which is thicker than that of A4 sheets for office laser printers. Together, this flexibility and the thick adhesive layer ensure higher adhesive strength and enable use on angular or round objects such as e.g. cables or hoses.

General ordering data

Version	THM, Device markers, 9 x 18 mm, white
Order No.	1059840000
Type	THM GEW 18/9 WS
GTIN (EAN)	4032248808267
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

THM GEW 18/9 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.3 mm	Depth (inches)	0.012 inch
Height	9 mm	Height (inches)	0.354 inch
Width	18 mm	Width (inches)	0.709 inch
Net weight	678 g		

Temperatures

Operating temperature range	-29...80 °C
-----------------------------	-------------

General data

Adhesive	Natural rubber adhesive	Approval acc. to UL 969	No
Colour	white	Halogen	No
Material	Cotton fabric	Material colour according to resistance code	9
Number of markers per combination	1 Label reel = Device markers	Number per roll	10,000
Number per sheet	10,000	Operating temperature range	-29...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-29 °C
Printing method	Thermal transfer	UL 94 flammability rating	V-0
Version	Self-adhesive	Width	18 mm

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format

Drawings



THM GEW 18/9 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1059840000](#)