

THM EL VIN 38 WS 30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Customised identification: EL

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the height can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

General ordering data

Version	THM, Device markers, 38 x , white
Order No.	1105560000
Type	THM EL VIN 38 WS 30M
GTIN (EAN)	4032248880775
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

THM EL VIN 38 WS 30M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	38 mm	Height (inches)	1.496 inch
Length	30,000 mm	Length (inches)	1,181.1 inch
Net weight	380 g		

Temperatures

Operating temperature range	-40...80 °C
-----------------------------	-------------

General data

Adhesive	Polyacrylate adhesive	Approval acc. to UL 969	No
Colour	white	Halogen	Yes
Length	30,000 mm	Material	Vinyl film
Number of markers per combination	1 Label reel = Device markers	Number per roll	1
Number per sheet	1	Operating temperature range	-40...80 °C
Operating temperature range, max.	80 °C	Operating temperature range, min.	-40 °C
Printing method	Thermal transfer	UL 94 flammability rating	HB
Version	Endless, Self-adhesive		

Device markers

Halogen	Yes
---------	-----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04		

Approvals

ROHS	Conform
------	---------

Downloads


Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format

THM EL VIN 38 WS 30M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



THM EL VIN 38 WS 30M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1105560000](#)