


THM ET S7 300-1 TU**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM ET S7 non-adhesive, roll-packaged labels are used to label the SIMATIC ET 200S and S7-modules from Siemens.

The M-Print® PRO software can be used to individually print the THM ET S7 labels with a THM printer. Labels can be easily separated. The THM MultiMark printer ensures highly-resistant printing.

General ordering data

Version	THM, Device markers, 103 x 22.6 mm, Siemens, Turquoise
Order No.	1161750000
Type	THM ET S7 300-1 TU
GTIN (EAN)	4032248950829
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

Creation date January 21, 2022 11:57:19 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.

THM ET S7 300-1 TU

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	103 mm	Height (inches)	4.055 inch
Width	22.6 mm	Width (inches)	0.89 inch
Net weight	466 g		

Temperatures

Operating temperature range	-50...100 °C
-----------------------------	--------------

General data

Application/manufacture	Siemens	Approval acc. to UL 969	No
Colour	Turquoise	Halogen	No
Material	Polypropylene	Number of markers per combination	1 Label reel = Device markers
Number per roll	500	Operating temperature range	-50...100 °C
Operating temperature range, max.	100 °C	Operating temperature range, min.	-50 °C
Printing method	Thermal transfer	UL 94 flammability rating	HB
Version	halogen-free	Width	22.6 mm

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04		

Approvals

ROHS	Conform
------	---------

Downloads


Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format

THM ET S7 300-1 TU

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



THM ET S7 300-1 TU**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1161750000](#)