

**CC-M 15/60 ST****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



MetalliCards are available in aluminium or stainless steel to meet a wide range of labelling requirements. The chrome-coated aluminium tags are the inexpensive alternative for a variety of applications, and in particular, they prove themselves through the deep contrasts of their multi-colour print.

In the technologically demanding chemical and process industries, you are on the safe side when using the stainless steel MetalliCard with its outstanding resistance characteristics. Its formats cover the needs of the entire system-identification spectrum. Whether small equipment or type plates, they ensure high-quality marking processes. The MetalliCard also offers optimum installation characteristics. MetalliCards can be used universally thanks to various fixation options: bonding, riveting, with tag holders or rails, or in combination with stainless steel cable ties.

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                                                 |
|------------|-------------------------------------------------|
| Version    | MetalliCard, Device markers, 15 x 60 mm, silver |
| Order No.  | <a href="#">1327720000</a>                      |
| Type       | CC-M 15/60 ST                                   |
| GTIN (EAN) | 4050118132595                                   |
| Qty.       | 200 pc(s).                                      |

## CC-M 15/60 ST

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.5 mm  | Depth (inches)  | 0.02 inch  |
| Height     | 15 mm   | Height (inches) | 0.591 inch |
| Width      | 60 mm   | Width (inches)  | 2.362 inch |
| Net weight | 3.412 g |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...130 °C |
|-----------------------------|--------------|

## General data

|                                   |                                |                                   |                                          |
|-----------------------------------|--------------------------------|-----------------------------------|------------------------------------------|
| Colour                            | silver                         | Material                          | Micro-etched stainless steel 1.4301 (ST) |
| Number of markers per combination | 1 MetalliCard = Device markers | Operating temperature range       | -55...130 °C                             |
| Operating temperature range, max. | 130 °C                         | Operating temperature range, min. | -55 °C                                   |
| Recommended industries            | Energy, Process                | Size of labelling field           | 15.2 x 57.2 mm                           |
| Width                             | 60 mm                          |                                   |                                          |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                  |                                          |
|------------------|------------------------------------------|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">EPLAN, WSCAD</a>             |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |


### CC-M 15/60 ST

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

### Example of use



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1327720000](#)