

SAIE-M8S-8-0.2U-FP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

General ordering data

Version	Built-in plugs, M8 thread, pin, straight, M 8, Number of poles: 8, 0.2 m
Order No.	1467590000
Type	SAIE-M8S-8-0.2U-FP
GTIN (EAN)	4050118273182
Qty.	1 pc(s).

SAIE-M8S-8-0.2U-FP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 9 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Technical data customisable plug-in connectors

Cable glands	M 8	Coding	none
Contact surface	Gold-plated	Housing main material	Brass, nickel-plated
Number of poles	8	Plugging cycles	≥ 100
Protection degree	IP67, when screwed in	Rated current	1.5 A
Rated voltage	30 V	Rated voltage	30 V
Temperature range of housing	-25...+85 °C	Type of connection	Pin

Standards

Connector standard IEC 61076-2-104

General data

Cable glands	M 8	Cable length	0.2 m
Coding	none	Conductor O.D.	-
Connection thread	M8 thread	Contact surface	Gold-plated
Core cross-section	0.14 mm ²	Housing main material	Brass, nickel-plated
Mounting thread	M8	Number of poles	8
Plugging cycles	≥ 100	Protection degree	IP67, when screwed in
Rated current	1.5 A	Rated voltage	30 V
Rated voltage	30 V	Strand / cable length	0.2 m
Temperature range of housing	-25...+85 °C	Type of connection	Pin
Wire cross section (Print/Online)	0,14 mm ²		

Classifications

ETIM 6.0	EC002635	ETIM 7.0	EC003570
ETIM 8.0	EC003570	ECLASS 9.0	27-44-01-03
ECLASS 9.1	27-44-01-03	ECLASS 10.0	27-44-01-03
ECLASS 11.0	27-44-01-03		

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

Creation date January 26, 2022 1:58:28 AM CET

Catalogue status 14.01.2022 / We reserve the right to make technical changes.


SAIE-M8S-8-0.2U-FP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany


www.weidmueller.com

Drawings

Wiring diagram



Pole scheme



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1467590000](#)