

THM ET 200SP 12.8/31 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM ET S7 non-adhesive, roll-packaged labels are used to label the SIMATIC ET 200S and S7-modules from Siemens.

The M-Print® PRO software can be used to individually print the THM ET S7 labels with a THM printer. Labels can be easily separated. The THM MultiMark printer ensures highly-resistant printing.

General ordering data

Version	THM, Device markers, 31 x 12.8 mm, Siemens, yellow
Order No.	1487690000
Type	THM ET 200SP 12.8/31 GE
GTIN (EAN)	4050118296518
Qty.	1 pc(s).
compatible printer	2599430000 2599440000

THM ET 200SP 12.8/31 GE

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	0.08 mm	Depth (inches)	0.003 inch
Height	31 mm	Height (inches)	1.22 inch
Width	12.8 mm	Width (inches)	0.504 inch
Net weight	438 g		

Temperatures

Operating temperature range	-50...100 °C
-----------------------------	--------------

General data

Application/manufacturer	Siemens	Approval acc. to UL 969	No
Colour	yellow	Halogen	No
Material	Polypropylene	Number of markers per combination	1 Label reel = Device markers
Number per roll	2,000	Operating temperature range	-50...100 °C
Operating temperature range, max.	100 °C	Operating temperature range, min.	-50 °C
Printing method	Thermal transfer	UL 94 flammability rating	HB
Version	halogen-free	Width	12.8 mm

Device markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04		

Approvals

ROHS	Conform
------	---------

Downloads


Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format

THM ET 200SP 12.8/31 GE

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



THM ET 200SP 12.8/31 GE**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

Type	RIBBON MM 110/360 SW	Version
Order No.	2005070000	Ink ribbon
GTIN (EAN)	4050118390049	
Qty.	1 pc(s).	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1487690000](#)