


**AP 90 GN 2043****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Flexible - More flexible - Profilform**

Modular housings in profile form - the flexible modular system comprising coloured and transparent plastic profiles and carrier modules

The combination of standard pitches mounted side by side in any arrangement and metre goods cut accurate to the millimetre creates the perfect balance between flexibility and economic efficiency:

- Pitch profiles with standard widths ranging from 5mm to 45mm allow the mounting of all standard PCB formats.
- Variable heights ensure maximum component density, even with larger electronics components.
- The different installation variations mean that mounting the enclosure directly is as easy as clipping components onto the terminal rail
- Solid hoods protect the module reliably from external influences

The recipe for success: variable profile + modular form components = flexible enclosure concept that offers a large surface area for the PCBs.

The modular concept is designed for modules with high space requirements and suitable for small component quantities and different widths.

**General ordering data**

|            |                                                                |
|------------|----------------------------------------------------------------|
| Version    | Electronics housings, RS 90 Pale green, End plate, Width: 5 mm |
| Order No.  | <a href="#">1504790000</a>                                     |
| Type       | AP 90 GN 2043                                                  |
| GTIN (EAN) | 4050118313239                                                  |
| Qty.       | 20 pc(s).                                                      |

## AP 90 GN 2043

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Height     | 16.9 mm | Height (inches) | 0.665 inch |
| Width      | 5 mm    | Width (inches)  | 0.197 inch |
| Net weight | 2.4 g   |                 |            |

## General data

|                   |            |                        |          |
|-------------------|------------|------------------------|----------|
| Colour            | Pale green | Colour chart (similar) | RAL 6021 |
| Protection degree | IP00       |                        |          |

## Material data

|                                  |           |                     |       |
|----------------------------------|-----------|---------------------|-------|
| Comparative Tracking Index (CTI) | 600 ≤ CTI | Insulating material | PA 66 |
| UL 94 flammability rating        | V-2       |                     |       |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001031    | ETIM 7.0    | EC001031    |
| ETIM 8.0    | EC001031    | ECLASS 9.0  | 27-18-27-90 |
| ECLASS 9.1  | 27-18-27-90 | ECLASS 10.0 | 27-18-27-92 |
| ECLASS 11.0 | 27-18-27-92 | ECLASS 12.0 | 27-18-27-92 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads



|                  |                                                                                                                                                                                                 |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Engineering Data | <a href="#">CAD data – STEP</a>                                                                                                                                                                 |
| Catalogues       | <a href="#">Catalogues in PDF-format</a>                                                                                                                                                        |
| Brochures        | <a href="#">FL ANALO.SIGN.CONV. EN</a><br><a href="#">MB DEVICE MANUF. EN</a><br><a href="#">FL MACHINE SAFETY EN</a><br><a href="#">FL 72H SAMPLE SER EN</a><br><a href="#">PO OMNIMATE EN</a> |

## AP 90 GN 2043

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1504790000](#)