

VP 16-EXE SW**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPK EX (Ex blanking plug in plastic), Blanking plug, in closed state, PG 16, 12 mm, IP66, IP68, Polyamide
Order No.	1569400000
Type	VP 16-EXE SW
GTIN (EAN)	4008190025779
Qty.	100 pc(s).

VP 16-EXE SW

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Length	17 mm	Length (inches)	0.669 inch
Diameter	22.5 mm	Net weight	4.4 g

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

Certificate numbers cable gland

Certificate no. cable gland (ATEX)	LCIE 08 ATEX 6085X	Certificate no. cable gland (IECEx)	IECEx LCI 08.0035X
Identification	Ex e II, Ex tD		

General information

AF size 1	27 mm	Cable glands	PG
Diameter of sealing ring	22.5 mm	External thread	PG 16
Halogen	No	Length of thread	12 mm
Material		Note: protection class	IP54 in accordance with EN 60529 standard, minimal without flat gasket; IP66 in accordance with EN 60529, minimal without flat gasket; IP68 in accordance with EN 60529 with flat gasket; Except for 2D application, as specified in the Ex-Certificate, a flat gasket is required for IP66.
	Polyamide		
Operating temperature range, max.	80 °C	Operating temperature range, min.	-20 °C
Protection degree	IP54, IP66	Protection degree with GWDR	IP66, IP68
Tightening torque	5.5 Nm	UL 94 flammability rating	V-2

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ECLASS 9.0	27-14-44-25
ECLASS 9.1	27-14-44-35	ECLASS 10.0	27-14-44-25
ECLASS 11.0	27-14-44-25	ECLASS 12.0	27-14-08-05

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format

VP 16-EXE SW

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold


Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1569400000](#)