

KV 29-M**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

Version	VG H (HDC halved cable gland), Cable glands, straight, PG 29, OD min. 18 - OD max. 27 mm, IP65, Brass, nickel-plated
Order No.	1656430000
Type	KV 29-M
GTIN (EAN)	4008190409449
Qty.	10 pc(s).

KV 29-M

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technical data

Dimensions and weights

Width	10 mm	Width (inches)	0.394 inch
Net weight	37.67 g		

Temperatures

Operating temperature	-20 °C...60 °C
-----------------------	----------------

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1	SCIP	e8f3dd16-18ca-4fe7-869b-76a12021
------------	----------------	------	----------------------------------

General information

AF size	37 mm	AF size 1	37 mm
Cable glands	PG	External thread	PG 29
Material	Brass, nickel-plated	Notch multi-layer sealing diameter 1	18 mm
Notch multi-layer sealing diameter 2	21 mm	Notch multi-layer sealing diameter 3	24 mm
Notch multi-layer sealing diameter 4	27 mm	O-Ring	NBR
Operating temperature range, max.	60 °C	Operating temperature range, min.	-20 °C
Outer cable diameter, max.	27 mm	Outer cable diameter, min.	18 mm
Pitch of thread	1.59 mm	Protection degree	IP65
Protection degree with GWDR	IP65	Sealing	NBR

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ECLASS 9.0	27-14-44-32
ECLASS 9.1	27-14-44-32	ECLASS 10.0	27-14-44-32
ECLASS 11.0	27-14-44-32	ECLASS 12.0	27-14-08-01

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1656430000](#)