

VP M20-EXE SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPK EX (Ex blanking plug in plastic), Blanking plug, in closed state, M 20, 15 mm, IP66, IP68, Polyamide
Order No.	1737080000
Type	VP M20-EXE SW
GTIN (EAN)	4008190956554
Qty.	100 pc(s).

VP M20-EXE SW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Length	19 mm	Length (inches)	0.748 inch
Diameter	20 mm	Net weight	3.71 g

Temperatures

Operating temperature	-20 °C...80 °C
-----------------------	----------------

Certificate numbers cable gland

Certificate no. cable gland (ATEX)	LCIE 08 ATEX 6085X	Certificate no. cable gland (IECEx)	IECEx LCI 08.0035X
Identification	Ex e II, Ex tD		

General information

AF size 1	23 mm	Cable glands	metric
Diameter of sealing ring	20 mm	External thread	M 20
Halogen	No	Length of thread	15 mm
Material		Note: protection class	IP54 in accordance with EN 60529 standard, minimal without flat gasket; IP66 in accordance with EN 60529, minimal without flat gasket; IP68 in accordance with EN 60529 with flat gasket; Except for 2D application, as specified in the Ex-Certificate, a flat gasket is required for IP66.
	Polyamide		
Operating temperature range, max.	80 °C	Operating temperature range, min.	-20 °C
Pitch of thread	1.5 mm	Protection degree	IP54, IP66
Protection degree with GWDR	IP66, IP68	Tightening torque	7 Nm
UL 94 flammability rating	V-2		

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ECLASS 9.0	27-14-44-25
ECLASS 9.1	27-14-44-35	ECLASS 10.0	27-14-44-25
ECLASS 11.0	27-14-44-25	ECLASS 12.0	27-14-08-05

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN, WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

Creation date September 16, 2022 10:18:07 AM CEST


Catalogue status 09.09.2022 / We reserve the right to make technical changes.

VP M20-EXE SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1737080000](#)