

**LM MT300 30/20 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration



- Adhesive polyester labels
- Suitable for A4 laser printers
- Abrasion-resistant
- High heat resistance
- For marking all kinds of switchgear and modules
- Can also be written on with a ballpoint pen or STI marking pen

**General ordering data**

|            |                                              |
|------------|----------------------------------------------|
| Version    | LaserMark, Device markers, 20 x 30 mm, white |
| Order No.  | <a href="#">1724161044</a>                   |
| Type       | LM MT300 30/20 WS                            |
| GTIN (EAN) | 4008190369019                                |
| Qty.       | 10 pc(s).                                    |

## LM MT300 30/20 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.08 mm | Depth (inches)  | 0.003 inch |
| Height     | 20 mm   | Height (inches) | 0.787 inch |
| Width      | 30 mm   | Width (inches)  | 1.181 inch |
| Net weight | 0.012 g |                 |            |

## Temperatures

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -40...150 °C |
|-----------------------------|--------------|

## General data

|                                   |                                   |                                              |               |
|-----------------------------------|-----------------------------------|----------------------------------------------|---------------|
| Adhesive                          | Acrylate adhesive                 | Approval acc. to UL 969                      | Yes           |
| Colour                            | white                             | Halogen                                      | No            |
| Material                          | Polyester, PVC-free               | Material colour according to resistance code | 9             |
| Number of markers per combination | 1 Label sheet = 78 Device markers | Number per sheet                             | 78            |
| Operating temperature range       | -40...150 °C                      | Operating temperature range, max.            | 150 °C        |
| Operating temperature range, min. | -40 °C                            | Printing method                              | Laser print   |
| UL 94 flammability rating         | HB                                | Version                                      | Self-adhesive |
| Width                             | 30 mm                             |                                              |               |

## Device markers

|         |    |
|---------|----|
| Halogen | No |
|---------|----|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 |             |             |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                  |                                          |
|------------------|------------------------------------------|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">EPLAN, WSCAD</a>             |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |

### LM MT300 30/20 WS

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1724161044](#)