

KLBUE CO 3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Shielding and earthing**

Our protective earth conductor and shielding terminals featuring different connection technologies allow you to effectively protect both people and equipment from interference, such as electrical or magnetic fields. A comprehensive range of accessories rounds off our range.

General ordering data

Version	Clamping yoke, Clamping yoke, Steel
Order No.	1749151001
Type	KLBUE CO 3
GTIN (EAN)	4032248064441
Qty.	10 pc(s).

KLBUE CO 3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	45 mm	Depth (inches)	1.772 inch
Height	25 mm	Height (inches)	0.984 inch
Width	24 mm	Width (inches)	0.945 inch
Mounting dimension - width	23 mm	Net weight	36.2 g

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	Steel	Colour	silver
----------	-------	--------	--------

System specifications

Version	For a shield connection
---------	-------------------------

Additional technical data

Explosion-tested version	No	Installation advice	Direct mounting, Busbar
Type of fixing	Snap-on		

Conductors for clamping (rated connection)

Cable diameter, max.	20 mm	Cable diameter, min.	10 mm
----------------------	-------	----------------------	-------

Dimensions

Pitch in mm (P)	25 mm
-----------------	-------

General

Installation advice	Direct mounting, Busbar
---------------------	-------------------------

Classifications

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ECLASS 9.0	27-14-11-50
ECLASS 9.1	27-14-11-50	ECLASS 10.0	27-14-11-50
ECLASS 11.0	27-14-11-50	ECLASS 12.0	27-14-11-50

Approvals

Approvals



ROHS	Conform
------	---------

KLBUE CO 3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of
Conformity

[EAC certificate](#)

Engineering Data

[CAD data – STEP](#)

Engineering Data

[EPLAN, WSCAD](#)

User Documentation

[Beipackzettel_KLBUE.pdf](#)
[StorageConditionsTerminalBlocks](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Weidmuller:](#)

[1749151001](#)